

Midea Commercial & VRF systems to BACnet MS/TP Interface

Item number: INBACMID001I100

The Midea-BACnet interface allows full bidirectional communication between Midea Commercial and VRF units and BACnet MS/TP networks. The interface enables BACnet communication via polling or subscription requests (COV), making the indoor unit available through independent BACnet objects.



Midea to BACnet MS/TP - 1 indoor unit

Features and benefits

- ✓ **BACnet MS/TP support only**
Only the BACnet MS/TP protocol is supported.
- ✓ **AC unit data served as fixed BACnet Objects**
Air conditioning unit properties and functionalities are abstracted into fixed BACnet Objects.
- ✓ **Total unit control and monitoring from BACnet**
Through internal variables, running hours counter (for maintenance purposes), and error indication.
- ✓ **Multiple mounting options**
Mounting options include DIN rail, wall, or, in some AC models, even inside the indoor unit.
- ✓ **Configuration from onboard DIP switches**
The interface configuration is carried out directly through its onboard DIP switches.
- ✓ **Occupancy function to allow energy savings**
Occupancy function that helps reduce costs, as HVAC systems are one of the main energy consumers.
- ✓ **AC unit control by remote and BACnet MS/TP**
The AC unit can simultaneously be controlled via BACnet MS/TP and its own remote controller.

Midea Commercial & VRF systems to BACnet MS/TP Interface



General	
Net Width (mm)	53
Net Height (mm)	58
Net Depth (mm)	93
Net Weight (g)	250
Packed Width (mm)	14
Packed Height (mm)	9
Packed Depth (mm)	10
Packed Weight (g)	320
Operating Temperature °C Min	0
Operating Temperature °C Max	60
Storage Temperature °C Min	-20
Storage Temperature °C Max	85
Power Consumption (W)	1.44
Input Voltage (V)	12 VDC
Power Connector	2-pole
Configuration	Dip-switches
Capacity	1 Indoor unit.
Installation Conditions	This gateway is designed to be mounted inside an enclosure. If the unit is mounted outside an enclosure, precautions should always be taken to prevent electrostatic discharge to the unit. When working inside an enclosure (e.g., making adjustments, setting switches, etc.), typical anti-static precautions should always be followed before touching the unit.
AC Model Compatibility	Midea Commercial & VRF systems

Midea Commercial & VRF systems to BACnet MS/TP Interface



General

Content of Delivery	Intesis Gateway, Installation Manual.
Mounting	DIN rail mount (bracket included), Wall mount
Housing Materials	Plastic
Warranty (years)	3 years
Packaging Material	Cardboard

Identification and Status

Product ID	INBACMID0011100
Country of Origin	Spain
HS Code	8517620000
Export Control Classification Number (ECCN)	EAR99

Physical Features


Connectors / Input / Output	Power supply, EIA-485, HVAC port.
LED Indicators	Gateway and communication status.
DIP & Rotary Switches	EIA-485 serial port configuration. Gateway settings.

Certifications and Standards

ETIM Classification	EC001604
WEEE Category	IT and telecommunications equipment



Use Case



Integration example.