





LOC	DIST	REVISIONS				
FT	0	REV	DATE	BY	APPV	
		M2	REVISED PER ECO-11-004820	11MAR11	RK	HMR



DETAIL A



DETAIL B



1. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
2. WILL ACCEPT SEVEN (7) TYPE XII SOCKET CONTACTS.
3. #4 FASTENER RECOMMENDED FOR MOUNTING.
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4 OBSOLETE

4-40 THREADED INSERTS	NO	A	206227-6
3.81±0.08 [.150±.003]	YES	A	206227-5
3.81±0.08 [.150±.003]	NO	B	206227-2
3.81±0.08 [.150±.003]	NO	A	206227-1

C		PERIPHERAL SEAL		SEE DETAIL		PART NUMBER					
THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN D.HARDY 05/31/94		 TE Connectivity							
		CHK W.G.LENKER 06/08/94									
DIMENSIONS:		APVD A.FRANTUM 07/13/94		NAME							
INCHES		PRODUCT SPEC		RECEPTACLE HOUSING, REVERSE SEX, SHELL SIZE 23, CPC							
		108-10024									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC									
0 PLC ± -											
1 PLC ± -											
2 PLC ± ± 0.13 [.005]				SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
3 PLC ± ± -				A1		00779		C=206227		-	
4 PLC ± ± -											
ANGLES											
FINISH		WEIGHT									
MATERIAL		-									
NYLON, BLACK											
		CUSTOMER DRAWING				SCALE		2:1		SHEET 1 of 1	
										REV M2	