

WINDOW-TYPE CURRENT TRANSFORMER, CLASS 1 400A/1A, 5VA PRIMARY CURRENT 400A, 5VA



Figure similar

Model		
Product designation		Window-type current transformers
Protection class		
Protection class IP		IP20
Connections		
Type of electrical connection / at output		screw-type terminals
Mechanical Design		
Height	mm	98
Width	mm	82.5
Width		
• of the push-through bus bar / at 1 bus bar / maximum	mm	50
• of the push-through bus bar / in case of 2 bus bars / maximum	mm	40
Depth	mm	80
Mounting type		screw fixing

Outer diameter / of the push-through conductor / maximum	mm	36
--	----	----

Environmental conditions

Ambient temperature

- during operation / minimum
- during operation / maximum

°C	-10
°C	55

Certificates

Equipment marking / acc. to DIN EN 61346-2

T

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/4NC5325-0CE20>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/4NC5325-0CE20/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=4NC5325-0CE20

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

09/05/2016