
**PWTR17-2RS-XL**

Galet de roulement

Yoke type track rollers PWTR..-2RS-XL, double row cylindrical roller bearings with particularly thick-walled outer ring, with a central rib, full complement cylindrical roller set and an inner ring, the outer ring is guided axially by the central rib and rolling elements, protected lip seal on both sides, X-life design

X-life

Information technique



Votre alternative produit actuelle

Joint	2RS	Joint frottant des deux côtés
profil bague extérieure	IOP	Profil INA optimisé
dispositif de lubrification	IR	Via la bague intérieure

dimensions principale & données de performance

d	17 mm	Alésage
D	40 mm	Diamètre extérieur
B	21 mm	Largeur, bague intérieure
C _{r w}	14.300 N	Charge dyn. de base, radiale
C _{0r w}	18.200 N	Charge stat. de base, radiale
C _{ur w}	2.200 N	Limite à la fatigue, radiale
n _{D G}	5.000 1/min	Vitesse pour une lubrification à la graisse
F _{0r per}	18.200 N	Charge radiale statique admissible
F _{r per}	16.400 N	Charge radial dynamique admissible sur bague extérieure
≈m	0,143 kg	Poids



Dimensions

C	20 mm	Largeur, bague extérieure
d 2	22 mm	Diamètre d'arrêt rondelle de butée
r min	1 mm	Dimension minimum de chanfrein
r 1 min	0,5 mm	Dimension minimum de chanfrein

Caractéristiques

-  Effort radial
-  Effort axial uni directionnel
-  Effort axial dans les 2 directions
-  Lubrification à vie, sans entretien
-  Lubrification à la graisse
-  Etanche des 2 côtés