

ENERGY AND AUTOMATION

HMI DISPLAY 7" TFT LCD 64K COLORS TOUCH-SCREEN, SUPPLY 12-24VDC, PORTS electric ETHERNET, RS232/RS485/RS422, USB. PROTOCOLS MODBUS RTU, MODBUS TCP, SIMATIC S7 ETHERNET, OPC UA AND MQTT




| Product designation | | | | HMI |
|----------------------------|-----------------------|----|---|---------------------------|
| Product type designation | | | | LRHA07 |
| Auxiliary supply voltage | | | | 24VDC |
| Power supply | | | | |
| Rated auxil. supply vol | tage | | | 24VDC |
| Operating voltage range | • | | | 1832VDC |
| Avarage current consu | | | mA | 300 |
| System resources | | | | |
| Display | | | | 7" TFT 16:9 |
| Colors | | | | 64K |
| Resolution | | | | 800x480 |
| Brightness | | | | 200Cd/m2 |
| Dimming | | | | Yes |
| Touchscreen | | | | Resistive |
| | | | | ARM Cortex A8 |
| CPU | | | | 1GHz |
| Operative system | | | Linux 3.12 | |
| Flash | | | 4GB | |
| RAM | | | | 512MB |
| Application memory | | | | 60MB |
| Real Time Clock | | | Yes | |
| Communications | | | | |
| Type of communication port | | | 1 Ethernet (10/100Mbit), 1 USB (Host v2.0, max 500mA) and 1 Serial (RS232, RS485, RS422 software configurable) | |
| Connections | | | | J. J. J. |
| | | | | Screw, |
| Terminals type | | | | extractable |
| Ambient conditions | | | | |
| Temperature | | | | |
| | Operating temperature | | | |
| | | ma | x °C | +50 |
| | Storage temperature | | | |
| | | mi | | -20 |
| | | ma | x °C | +70 |
| Relative humidity % | | | % | 585% without condensation |
| Maximum Pollution degree | | | 2 | |
| Housing | | | | |
| Mounting | | | | Flush mount |




ENERGY AND AUTOMATION


HMI DISPLAY 7" TFT LCD 64K COLORS TOUCH-SCREEN, SUPPLY 12-24VDC, PORTS electric ethernet, RS232/RS485/RS422, USB. PROTOCOLS MODBUS RTU, MODBUS TCP, SIMATIC S7 ETHERNET, OPC UA AND MQTT

| Degree of protection | | IP66, type 2, 4X (front); IP20 (rear) |
|------------------------|----|---|
| Dimensions (W x H x D) | mm | 187 x 147 x 34 |
| Weight | g | 600 |
| | | |






Wiring diagrams



- Serial port (type RS232, RS485, RS422 software configurable)
- Ethernet port
- 2 3 4 **USB** port
- Power supply



Certifications and compliance

Compliance

emissions EN 61000-6-3

EN 61000-6-4

immunity EN 61000-6

immunity EN 61000-6-2 for installation in industrial environments

Certificates

cULus

RCM