

# Hole Puncher XGT®

## PP001G

40Vmax, 20 mm

Model PP001G is a Hole Puncher powered by a 40Vmax XGT® Li-Ion battery

Main feature and benefits: Using the 40Vmax XGT® Li-Ion battery the punching speed has been improved. With the Brushless motor the working time has been reduced by 35%. Maximum punching capacity: Ø20mm (t=9mm) (Round hole only: Ø19mm (t=10mm).



### Technical specifications

|                                            |                        |
|--------------------------------------------|------------------------|
| Voltage XGT                                | ✓                      |
| Nominal Battery Voltage                    | 40 V                   |
| Battery Chemistry (Ni-Cd / Ni-MH / Li-ion) | Li-ion                 |
| Max. Throat Depth                          | 40 mm                  |
| Hole Shape                                 | Round / Oblong         |
| Max. Hole Size (stainless steel)           | Ø20 / t6 mm            |
| Max. Hole Size (mild steel)                | Ø20 / t9 mm            |
| Sound Pressure Level (L <sub>pA</sub> )    | 77 dB(A)               |
| Product net weight                         | 10,9 kg                |
| Noise Uncertainty (K Factor)               | 3 dB(A)                |
| Tool weight with battery                   | 11,6 - 11,96 kg        |
| Product Dimensions (L x W x H):            | 398 x 129 x 315 mm     |
| Vibration Level (3 axes)                   | ≤ 2,5 m/s <sup>2</sup> |
| Vibration Uncertainty (K Factor)           | 1,5 m/s <sup>2</sup>   |
| Brushless Motor                            | ✓                      |

Link to product - [www.makitauk.com](http://www.makitauk.com)



# Related products

## Other

User manual

Parts drawing