



Technical data

4T-25877/25821


Single row tapered roller bearings

Tapered roller bearing, pressed steel cage


KIT CONTENT

4T-25877, 4T-25821

VISUAL (S)



4T-25877/25821
Single row tapered roller bearings



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	34,925 mm
D - External diameter	73,025 mm
B - Bearing/Inner ring width	24,608 mm
C - Outer ring width	19,05 mm
T - Total width	23,812 mm
d1 - External diameter inner ring	53 mm
a - Charge load application point	15,712 mm
Mass	0,473 kg

PRODUCT PERFORMANCE	
C - Dynamic load	78,5 kN
C0 - Static load	85 kN
Cu - Fatigue limit load	10,4 kN

PRODUCT PERFORMANCE

A2 - Rating life coefficient	1
e - Coefficient	0.29
Y0 - Static axial load coefficient	1.14
Y2 - Upper axial load coefficient	2.07
N lim - Oil lubrication limit speed	7100 tr/min
N lim - Grease lubrication limit speed	5300 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	40,5 mm
db min - Min IR shoulder diameter	43 mm
Da max - Max shoulder diameter OR	65 mm
Db min - Min OR shoulder diameter	68 mm
ra max - Max fillet radius	1,5 mm
r1a - Max fillet radius	0,8 mm

KIT COMPONENT

Cone designation	4T-25877
Cup designation	4T-25821

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-25877/25821
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No



ESHOPDONOTDISPLAY

Rolling element material

Acier de cémentation

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

Fa / Fr ≤ e		Fa / Fr > e	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_o = X_o.F_r + Y_o.F_a$

X _o	Y _o
0.5	Y0

If $P_o \leq F_r$, then use $P_o = F_r$

The values for e, Y2 and Y0 are shown in the above table

