

WMS 25,4 (EX40)R - Shrink sleeve



0800296

<https://www.phoenixcontact.com/gb/products/0800296>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLLMASTER 300/600, THERMOMARK ROLL X1, THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK W, THERMOMARK X1.2, cable diameter range: 8.5 ... 25.4 mm, unperforated, mounting type: slide-on, Number of individual labels: 1, roll length: 15 m, text field height: 40 mm, text field width: 15000 mm

Product description

The continuous shrink sleeves in the WMS... product family can be assembled to create individual marker lengths using the THERMOMARK E. CUTTER or E.CUTTER/P. After the printing, assembly, and applying process, you have the option of shrinking the marked shrink sleeves by applying heat manually and thus fixing them on the cable/wire.

Your advantages

- Permanent and captive identification of single-core wires, wires, cables, pneumatic hoses, and other cylindrical objects
- High flexibility, as individual marker lengths ranging from 3.45 mm ... 2000 mm (0.14" ... 78.7") can be realized in combination with the cutter and perforation cutter
- As an option, the sleeves can be shrunk by applying heat manually to fix the sleeve in position
- High diameter coverage with a shrink ratio of 3:1
- Widely used and proven worldwide in control cabinet and machine building, the oil and gas industry, and the railway industry

Commercial data

Item number	0800296
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG2216
Product key	BG2216
Catalog page	Page 226 (C-3-2019)
GTIN	4046356625869
Weight per piece (including packing)	666.2 g
Weight per piece (excluding packing)	572.4 g
Customs tariff number	39173200
Country of origin	CN

WMS 25,4 (EX40)R - Shrink sleeve

0800296

<https://www.phoenixcontact.com/gb/products/0800296>



Technical data

Notes

Note on application	For the THERMOMARK ROLL and THERMOMARK ROLL 2.0 roll printers, this material can only be processed with an external media hub.
Material information	The specified minimum wire diameter of the shrink sleeve refers to its use as a marking material and does not guarantee any insulation characteristics once shrunk. Depending on the processed material batch, as well as the storage and processing conditions, the maximum insertable wire diameter may be reduced.

Product properties

Product type	Shrink sleeve
Type	Shrink sleeve

Marking

Number of individual labels	1
Identification technology	Thermal transfer for rolls

Dimensions

Width	40 mm
Length of roll	15.00 m

External dimensions

Outside diameter	8.5 mm ... 25.4 mm
------------------	--------------------

Text field

Text field width	15000 mm
Text field height	40 mm

Material specifications

Color	white (RAL 9010)
Material	Polyolefine
Base element material	polyolefine
Shrink rate	3:1
Components	halogen-free
Shrink temperature	> 85 °C

Cable/line

External cable diameter	8.5 mm ... 25.4 mm
-------------------------	--------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

WMS 25,4 (EX40)R - Shrink sleeve



0800296

<https://www.phoenixcontact.com/gb/products/0800296>

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilem test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

WMS 25,4 (EX40)R - Shrink sleeve



0800296

<https://www.phoenixcontact.com/gb/products/0800296>

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	5 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

WMS 25,4 (EX40)R - Shrink sleeve



0800296

<https://www.phoenixcontact.com/gb/products/0800296>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/0800296>



CSA

Approval ID: 252259



cULus Recognized

Approval ID: E310982_Vol2_Sec1

WMS 25,4 (EX40)R - Shrink sleeve



0800296

<https://www.phoenixcontact.com/gb/products/0800296>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WMS 25,4 (EX40)R - Shrink sleeve



0800296

<https://www.phoenixcontact.com/gb/products/0800296>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk