




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

- 5 FINISH: 200 MICROINCHES MIN. SILVER OVER 40 MICROINCHES MIN. NICKEL.
6. ALL DIMENSIONS ARE REFERENCE ONLY.



RETENTION CLIP
MATERIAL: STAINLESS STEEL



LOC	DIST			REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
CH	11	P	F		D	EC 0B20-0791-98	30/JUN/98	DAP
					C	EC 0B20-0671-98	27/MAY/98	RNP
					B	EC 0B20-0503-98	09/APR/98	RNP
					A	ECN 95011203	01-12-95	CMS

1. MATERIAL: COPPER ALLOY
2. FINISH: 30 MICROINCHES MIN. GOLD OVER 50 MICROINCHES MIN. NICKEL.
3. WIRE BARREL WILL ACCEPT #8 AWG WIRE
4. MATES WITH AMP P/N 193990-X.

OBSOLETE
OBSOLETE


5	15.7 [.62]	193991-4
5	25.4 [1.00]	193991-3
2	15.7 [.62]	193991-2
2	25.4 [1.00]	193991-1
FINISH	A	PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± -
ANGLES ± -

MATERIAL



FINISH



DR 04-13-94
D.A.P.

CHK -

APPD -

APPD -

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT -

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

PIN ASSEMBLY, TYPE XII
HIGH CURRENT #8 AWG

SIZE



CAGE CODE

00779

DRAWING NO

C-193991

SCALE

SHEET

1 OF 1