


Seven darlington array

Features

- Seven darlington pairs per package
- Output current 500 mA per driver (600 mA peak)
- Output voltage 50 V
- Integrated suppression diodes for inductive loads
- Outputs can be paralleled for higher current
- TTL/CMOS/PMOS/DTL Compatible inputs
- Inputs pinned opposite outputs to simplify layout



Description

The ULN2001, ULN2002, ULN2003 and ULN2004 are high voltage, high current darlington arrays each containing seven open collector darlington pairs with common emitters. Each channel rated at 500 mA and can withstand peak currents of 600 mA. Suppression diodes are included for inductive load driving and the inputs are pinned opposite the outputs to simplify board layout.

The versions interface to all common logic families:

- ULN2001 (general purpose, DTL, TTL, PMOS, CMOS)
- ULN2002 (14-25V PMOS)
- ULN2003 (5V TTL, CMOS)
- ULN2004 (6-15V CMOS, PMOS)

These versatile devices are useful for driving a wide range of loads including solenoids, relays DC motors, LED displays filament lamps, thermal printheads and high power buffers.

The ULN2001A/2002A/2003A and 2004A are supplied in 16 pin plastic DIP packages with a copper leadframe to reduce thermal resistance. They are available also in small outline package (SO-16) as ULN2001D1/2002D1/2003D1/2004D1.

Table 1. Device summary


| Order code | |
|------------|----------------|
| ULN2001A | ULN2001D1013TR |
| ULN2002A | ULN2002D1013TR |
| ULN2003A | ULN2003D1013TR |
| ULN2004A | ULN2004D1013TR |

Contents

| | | |
|---|----------------------------------|----|
| 1 | Diagram | 3 |
| 2 | Pin configuration | 4 |
| 3 | Maximum ratings | 5 |
| 4 | Electrical characteristics | 6 |
| 5 | Test circuits | 7 |
| 6 | Package mechanical data | 9 |
| 7 | Order code | 12 |
| 8 | Revision history | 13 |


1 Diagram

Figure 1. Schematic diagram



2 Pin configuration

Figure 2. Pin connections (top view)



3 Maximum ratings

Table 2. Absolute maximum ratings

| Symbol | Parameter | Value | Unit |
|-----------|--|-------------|------|
| V_O | Output voltage | 50 | V |
| V_I | Input voltage (for ULN2002A/D - 2003A/D - 2004A/D) | 30 | V |
| I_C | Continuous collector current | 500 | mA |
| I_B | Continuous base current | 25 | mA |
| T_A | Operating ambient temperature range | - 20 to 85 | °C |
| T_{STG} | Storage temperature range | - 55 to 150 | °C |
| T_J | Junction temperature | 150 | °C |

Table 3. Thermal data

| Symbol | Parameter | DIP-16 | SO-16 | Unit |
|------------|---|--------|-------|------|
| R_{thJA} | Thermal resistance junction-ambient, Max. | 70 | 120 | °C/W |

4 Electrical characteristics

Table 4. Electrical characteristics
($T_A = 25^\circ\text{C}$ unless otherwise specified).

| Symbol | Parameter | Test condition | Min. | Typ. | Max. | Unit |
|---------------|--|---|------|------|------|---------------|
| I_{CEX} | Output leakage current | $V_{CE} = 50\text{ V}$, (Figure 3.) | | | 50 | μA |
| | | $T_A = 70^\circ\text{C}$, $V_{CE} = 50\text{ V}$ (Figure 3.) | | | 100 | |
| | | $T_A = 70^\circ\text{C}$ for ULN2002, $V_{CE} = 50\text{ V}$, $V_I = 6\text{ V}$ (Figure 4.) | | | 500 | |
| | | $T_A = 70^\circ\text{C}$ for ULN2002, $V_{CE} = 50\text{ V}$, $V_I = 1\text{ V}$ (Figure 4.) | | | 500 | |
| $V_{CE(SAT)}$ | Collector-emitter saturation voltage (Figure 5.) | $I_C = 100\text{ mA}$, $I_B = 250\text{ }\mu\text{A}$ | | 0.9 | 1.1 | V |
| | | $I_C = 200\text{ mA}$, $I_B = 350\text{ }\mu\text{A}$ | | 1.1 | 1.3 | |
| | | $I_C = 350\text{ mA}$, $I_B = 500\text{ }\mu\text{A}$ | | 1.3 | 1.6 | |
| $I_{I(ON)}$ | Input current (Figure 6.) | for ULN2002, $V_I = 17\text{ V}$ | | 0.82 | 1.25 | mA |
| | | for ULN2003, $V_I = 3.85\text{ V}$ | | 0.93 | 1.35 | |
| | | for ULN2004, $V_I = 5\text{ V}$ | | 0.35 | 0.5 | |
| | | $V_I = 12\text{ V}$ | | 1 | 1.45 | |
| $I_{I(OFF)}$ | Input current (Figure 7.) | $T_A = 70^\circ\text{C}$, $I_C = 500\text{ }\mu\text{A}$ | 50 | 65 | | μA |
| $V_{I(ON)}$ | Input voltage (Figure 8.) | $V_{CE} = 2\text{ V}$, for ULN2002 $I_C = 300\text{ mA}$ | | | 13 | V |
| | | for ULN2003 $I_C = 200\text{ mA}$ | | | 2.4 | |
| | | $I_C = 250\text{ mA}$ | | | 2.7 | |
| | | $I_C = 300\text{ mA}$ | | | 3 | |
| | | for ULN2004 $I_C = 125\text{ mA}$ | | | 5 | |
| | | $I_C = 200\text{ mA}$ | | | 6 | |
| | | $I_C = 275\text{ mA}$ | | | 7 | |
| | | $I_C = 350\text{ mA}$ | | | 8 | |
| h_{FE} | DC Forward current gain (Figure 5.) | for ULN2001, $V_{CE} = 2\text{ V}$, $I_C = 350\text{ mA}$ | 1000 | | | |
| C_I | Input capacitance | | | 15 | 25 | pF |
| t_{PLH} | Turn-on delay time | $0.5 V_I$ to $0.5 V_O$ | | 0.25 | 1 | μs |
| t_{PHL} | Turn-off delay time | $0.5 V_I$ to $0.5 V_O$ | | 0.25 | 1 | μs |
| I_R | Clamp diode leakage current (Figure 9.) | $V_R = 50\text{ V}$ | | | 50 | μA |
| | | $T_A = 70^\circ\text{C}$, $V_R = 50\text{ V}$ | | | 100 | |
| V_F | Clamp diode forward voltage (Figure 10.) | $I_F = 350\text{ mA}$ | | 1.7 | 2 | V |

5 Test circuits

Figure 3. Output leakage current




Figure 4. Output leakage current (for ULN2002 only)




Figure 5. Collector-emitter saturation voltage Figure 6. Input current (ON)





Figure 7. Input current (OFF)




Figure 8. Input voltage




Figure 9. Clamp diode leakage current




Figure 10. Clamp diode forward voltage




Figure 11. Collector current vs input current




Figure 12. Collector current vs saturation voltage




Figure 13. Peak collector current vs duty cycle





Figure 14. Peak collector current vs duty cycle




6 Package mechanical data

In order to meet environmental requirements, ST offers these devices in ECOPACK[®] packages. These packages have a Lead-free second level interconnect. The category of second Level Interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97. The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark. ECOPACK specifications are available at: www.st.com.

Plastic DIP-16 (0.25) mechanical data

| Dim. | mm. | | | inch. | | |
|------|------|-------|------|-------|-------|-------|
| | Min. | Typ. | Max. | Min. | Typ. | Max. |
| a1 | 0.51 | | | 0.020 | | |
| B | 0.77 | | 1.65 | 0.030 | | 0.065 |
| b | | 0.5 | | | 0.020 | |
| b1 | | 0.25 | | | 0.010 | |
| D | | | 20 | | | 0.787 |
| E | | 8.5 | | | 0.335 | |
| e | | 2.54 | | | 0.100 | |
| e3 | | 17.78 | | | 0.700 | |
| F | | | 7.1 | | | 0.280 |
| I | | | 5.1 | | | 0.201 |
| L | | 3.3 | | | 0.130 | |
| Z | | | 1.27 | | | 0.050 |




P001C

Table 5. SO-16 Narrow mechanical data

| Dim. | mm. | | | inch. | | |
|------|-----------|------|------|--------|-------|-------|
| | Min. | Typ. | Max. | Min. | Typ. | Max. |
| A | | | 1.75 | | | 0.069 |
| a1 | 0.1 | | 0.25 | 0.004 | | 0.009 |
| a2 | | | 1.6 | | | 0.063 |
| b | 0.35 | | 0.46 | 0.014 | | 0.018 |
| b1 | 0.19 | | 0.25 | 0.007 | | 0.010 |
| C | | 0.5 | | | 0.020 | |
| c1 | | | 45° | (typ.) | | |
| D(1) | 9.8 | | 10 | 0.386 | | 0.394 |
| E | 5.8 | | 6.2 | 0.228 | | 0.244 |
| e | | 1.27 | | | 0.050 | |
| e3 | | 8.89 | | | 0.350 | |
| F(1) | 3.8 | | 4.0 | 0.150 | | 0.157 |
| G | 4.60 | | 5.30 | 0.181 | | 0.208 |
| L | 0.4 | | 1.27 | 0.150 | | 0.050 |
| M | | | 0.62 | | | 0.024 |
| S | 8° (max.) | | | | | |

Figure 15. Package dimensions



0016020 D

7 Order code

Table 6. Order code

| Part numbers | Package |
|---------------------|----------------------|
| ULN2001A | DIP-16 |
| ULN2002A | DIP-16 |
| ULN2003A | DIP-16 |
| ULN2004A | DIP-16 |
| ULN2001D1013TR | SO-16 in Tape & Reel |
| ULN2002D1013TR | SO-16 in Tape & Reel |
| ULN2003D1013TR | SO-16 in Tape & Reel |
| ULN2004D1013TR | SO-16 in Tape & Reel |

8 Revision history

Table 7. Revision history

| Date | Revision | Changes |
|-------------|----------|--|
| 05-Dec-2006 | 5 | Order code updated and document reformatted. |
| 28-Aug-2007 | 6 | Added Table 1 . in cover page. |

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2007 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com