



**FAG****6228-J20AA-C3** [🔗](#)

Deep groove ball bearing

Deep groove ball bearing 62...J20AA, single row, steel sheet metal cage, ceramic coated

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S1	Rings dimensional stabilized up to 200°
Lubricant	Without	Bearing not greased
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Coating	J20AA	current insulation, outer ring ceramic coated
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	140 mm	Bore diameter
D	250 mm	Outside diameter
B	42 mm	Width
C _r	188,000 N	Basic dynamic load rating, radial
C _{0r}	165,000 N	Basic static load rating, radial
C _{ur}	8,400 N	Fatigue load limit, radial
n _G	3,600 1/min	Limiting speed
n _{gr}	3,600 1/min	Reference speed
≈m	8 kg	Weight



Mounting dimensions

$d_{a\min}$	154 mm	Minimum diameter shaft shoulder
$D_{a\max}$	236 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2.5 mm	Maximum fillet radius

Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
D_1	214.4 mm	Shoulder diameter outer ring
d_1	175.9 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

f_0	14.9	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Current insulated