

THS1550RJ

✓ ACTIVE

CGS | CGS THS

TE Internal #: 2-1879074-3

50 ohm Chassis Mount Resistor, 15 W, Wire Wound, 2

Terminations, ±50 ppm/°C, 5 %, Solder Lug, Loose Piece - Tray, 11 mm [.433 in] Height, CGS THS

[View on TE.com >](#)



Passive Components > Resistors > Chassis Mount Resistors > Power Resistor: Aluminum Housed, 75 Watt



Resistor Type: **Power Resistor**

Resistance Class: **Up to 1kΩ**

Resistance Value: **50 Ω**

Power Rating: **15 W**

Element Type: **Wire Wound**

[All Power Resistor: Aluminum Housed, 75 Watt \(236\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	265 VDC
Resistance Class	Up to 1kΩ
Resistance Value	50 Ω
Power Rating	15 W
Passive Component Tolerance	5 %

Termination Features

Number of Terminations	2
Chassis Mount Resistor Termination Type	Solder Lug

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
--------------------------	----------------------------

Dimensions

--	--



Product Height	11 mm[.433 in]
Product Length	36.5 mm[1.437 in]
Product Width	21 mm[.827 in]

Usage Conditions

Temperature Coefficient	±50 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Loose Piece - Tray
------------------	--------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-C339-T419
Power Resistor: Aluminum Housed, 75 Watt

Also in the Series | CGS THS



Chassis Mount Resistors(241)



PCI & PCI Express Connectors(8)

Customers Also Bought



TE Part #52929-1
PIDG SP SPD 22-16COMM22-18MIL6




TE Part #1-480699-9
02P UMNL CAP HSG BLK



TE Part #1-480698-9
02P UMNL PLUG HSG BLK



TE Part #2108857-4
PCB Ant, MHF, 200mm, Wi-Fi 6E TripleBand



TE Part #179463-1
POWER DBL LOCK CAP HSG F/H 2P




TE Part #41619
250 FASTON TAB BR



TE Part #60279-2
250 FASTON REC 18-14 AWG TPBR



TE Part #T4043014041-000
M8.FMLE.PNLFRONT.4POS.STRPCB



TE Part #2-826629-0
20P AMPMODU II PIN HDR



TE Part #63705-1
125 FASTON REC 22-18 AWG BR



Documents

Product Drawings

THS15 50R 5%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1879074-3_BB.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1879074-3_BB.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1879074-3_BB.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

Aluminium Housed Power Resistors - Type THS Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English