

**FAG****6322-2Z**

Deep groove ball bearing

Deep groove ball bearing 63...-2Z, single row, shields, steel sheet metal cage

Technical information



Your current product variant

Sealing	2Z	Non-contact shield on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	GA13	Ball bearing and insert bearing grease, standard for D>62mm
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	240 mm	Outside diameter
B	50 mm	Width
C _r	201,000 N	Basic dynamic load rating, radial
C _{0r}	165,000 N	Basic static load rating, radial
C _{ur}	8,800 N	Fatigue load limit, radial
n _G	3,250 1/min	Limiting speed
n _{gr}	4,150 1/min	Reference speed
m	9.981 kg	Weight



Mounting dimensions

$d_{a\ min}$	124 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	226 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2.5 mm	Maximum fillet radius

Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
D_1	197.54 mm	Shoulder diameter outer ring
D_2	203.14 mm	Caliber diameter outer ring
d_1	152.85 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

f_0	13.8	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides