




RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
A0		2024.06.28	Initial Release	LENA

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Terminal Body: PA66,
- Item ② Terminal lever: PBT ,
- Item ③ Terminal Cover: PA66 ,
- Item ④ Spring: Stainless
- Item ⑤ Terminal Contact: Copper alloy,

Electrical: UL1059 Group B/G Group C Group D Group F

- Voltage rating: 300 V 150 V 300V 400V
- Current rating: 16A 16A 16A 16A
- Wire range:
 - Solid wire: 24-12AWG
 - Stranded wire: 24-12AWG
- Wire strip length: 11-13 mm
- Withstanding Voltage: 1.6KV AC
- Insulation Resisance: DV500V 500MQ min
- Operating temperature: -20°C to +105°C
- Assembling temperature: -5°C to +105°C
- Safety Approval: 

Part No. QT xx B DP x x H xxxx G

NO. OF POLES
02: 2 POLES
03: 3 POLES
16: 16 POLES

Body color
0: Black
1: Natural color
2: Red
3: Orange
4: Yellow
5: Green (RAL6018/T)
6: Blue
8: Grey (標準色)
9: White
C: Green (RAL 6018/U)

Lever color
0: Black
1: Natural color
2: Red
3: Orange (標準色)
4: Yellow
5: Green (RAL6018/T)
6: Blue
8: Grey
9: White
C: Green (RAL 6018/U)

RoHS compliant
(lead<4%)
In copper Alloy
00x0: "@" Logo (Standard)
00xA: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		QT series 180D pitch 7.5mm PCB terminal block				
PART NO.	QTxxBDPx x H xxxxG			DWG NO.	8QT0005	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
Roy 2024.11.07	Roy 2024.11.07	Lena 2024.06.28	Lena 2024.06.28		UNIT: mm	X. ±0.50
					SCALE: 2:1	X.X ±0.30
					REV.: A0	X.XX ±0.10
				SHEET: 01/01		X° ±1°