

Product data sheet

Characteristics

C4032D400

trip unit MicroLogic 2.3 for ComPacT NSX
400/630 circuit breakers, electronic, rating
400A, 3 poles 3d



Main

Range	ComPacT new generation
Range of product	ComPacT NSX400...630 new generation
Product or component type	Trip unit
Trip unit name	Micrologic 2.3
Trip unit technology	Electronic
Range compatibility	ComPacT new generation NSX400 ComPacT new generation NSX630
Device application	Distribution
Poles description	3P
Protected poles description	3D
Trip unit protection functions	LSol
Protection type	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection
Trip unit rating	400 A at 40 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Circuit breaker mounting mode	Fixed

Complementary

Long-time pick-up adjustment type Ir (thermal protection)	Adjustable 9 settings
[Ir] long-time protection pick-up adjustment range	160...400 A
Long-time protection delay adjustment type tr	Fixed
[tr] long-time protection delay adjustment range	11 S at 7.2 x Ir 16 S at 6 x Ir 400 s at 1.5 x Ir
Thermal memory	20 minutes before and after tripping
Short-time protection pick-up adjustment type lsd	Adjustable 9 settings
[lsd] Short-time protection pick-up adjustment range	1.5...10 x Ir
Short-time protection delay adjustment type tsd	Fixed
Instantaneous protection pick-up adjustment type li	Fixed
[li] instantaneous protection pick-up adjustment range	4800 A
Earth-leakage protection	Without
Zone selective interlocking ZSI	Without
Local signalling	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload

Environment

Standards	EN/IEC 60947-2
Electrical shock protection class	Class II
Pollution degree	3 conforming to IEC 60947-1
IP degree of protection	IP40 conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	17.5 cm
Package 1 Length	20.5 cm
Package 1 Weight	1.401 kg
Unit Type of Package 2	P06
Number of Units in Package 2	32
Package 2 Height	74.0 cm
Package 2 Width	60.0 cm
Package 2 Length	80.0 cm
Package 2 Weight	55.0 kg
Unit Type of Package 3	S03
Number of Units in Package 3	4
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	7.556 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------