

(Tile Mount)
Patent Pending
CFD69383P



(Hard Ceiling Mount)
Patent Pending CFD69383P1

These 2-port MIMO indoor wideband omnidirectional low-profile ceiling mount antennas are designed to provide pattern coverage optimized for indoor coverage requirements at 698-960 MHz and 1690-4000 MHz for the LTE, AWS-3, WCS, and CBRS/WiMAX frequency bands. The CFD69383P/CFD69383P1 are applicable for environments where aesthetics and wide-angle coverage are necessary for successful wireless deployment. Their small size and low profile enable maximum mounting flexibility while maintaining desired in-building aesthetics.

FEATURES AND BENEFITS

- Ultra-low profile
- 2-port MIMO for multipath mitigation
- Optimized performance using Laird proprietary tools
- Supports AWS-3 frequency band
- Mounts directly and easily to ceiling tile (CFD69383P1 is for hard ceiling mount installations)

ELECTRICAL SPECIFICATIONS											
Operating Frequency (MHz)	698-806	824-894	880-890	1350-1550	1690-1880	1850-1990	1910-2180	2300-2500	2500-2700	3300-3800	3800-4000
VSWR – Avg	<1.4:1	<1.4:1	<1.4:1	<1.7:1	<1.7:1	<1.6:1	<1.4:1	<1.3:1	<1.7:1	<1.7:1	<1.5:1
VSWR – Max	<1.5:1	<1.5:1	<1.5:1	<2.0:1	<1.8:1	<1.8:1	<1.8:1	<1.8:1	<1.8:1	<2.0:1	<2.0:1
Gain – Typ (dBi)	3.2	3.4	3.8	3.0	4.2	3.9	4.6	4.6	5.2	4.3	4.9
Gain – Max (dBi)	3.8	3.7	4.2	5.0	4.7	4.3	6.0	5.0	5.7	5.1	5.4
PIM - 2x20W – Avg (dBc)	< -158 (LTE low band)			< -160 (LTE high band)							
PIM - 2x20W – Max (dBc)	< -150 (LTE low band)			< -150 (LTE high band)							
Isolation – Avg (dB)	>20	>22	>23	>16	>16	>18	>19	>31	>36	>28	>30
Isolation – Max (dB)	>18	>18	>18	>13	>15	>15	>15	>25	>28	>25	>25
Nominal Impedance (Ohms)	50										
Max Power - Ambient 25°C (W)	50										
Polarization	Linear Horizontal										
Azimuth 3 dB Beamwidth	360°, Omnidirectional										


MECHANICAL SPECIFICATIONS	
Dimensions – height x diameter – mm (in.)	7.6 x 250 (0.3 x 9.84)
Weight – g (lbs.)	420 (0.93)
Antenna Color	White
Radome Material	PC, UL94-V0

ENVIRONMENTAL SPECIFICATIONS	
Operating Environment (Indoor or Outdoor)	Indoor
Operating Temperature – C° (F°)	-30 to +70C° (-22 to +158F°)
Storage Temperature – C° (F°)	-40 to +85C° (-40 to +185F°)
Material Substance Compliance	RoHS


CONFIGURATION

PART NUMBER	CABLE LENGTH	CONNECTOR	MOUNTING	PACKAGING
CFD69383P-30NF	30 cm (12 in.)	Type N-female	Ceiling tile	Unit
CFD69383P-30D43F	30 cm (12 in.)	4.3-10 female	Ceiling tile	Unit
CFD69383P-30D43F	30 cm (12 in.)	Type N-female	Ceiling tile	Bulk
CFD69383P-B30D43F	30 cm (12 in.)	4.3-10 female	Ceiling tile	Bulk
CFD69383P1-30NF	30 cm (12 in.)	Type N-female	Hard ceiling	Unit
CFD69383P1-30D43F	30 cm (12 in.)	4.3-10 female	Hard ceiling	Unit
CFD69383P1-B30NF	30 cm (12 in.)	Type N-female	Hard ceiling	Bulk
CFD69383P1-B30D43F	30 cm (12 in.)	4.3-10 female	Hard ceiling	Bulk

RADIATION PATTERNS



RADIATION PATTERNS



Americas: +1.847 839.6925
IAS-AmericasSales@lairdtech.com
Europe: +44.1628.858941
IAS-EUSales@lairdtech.com
Asia: IAS-AsiaSales@lairdtech.com
Middle East and Africa: +44.1628.858941
IAS-MEAUSales@lairdtech.com
www.lairdtech.com



Laird warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations Laird will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the Laird product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

Any information furnished by Laird Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2018 Laird Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Logo, and other marks are trademarks or registered trademarks of Laird Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.

