

KUP-14A55-24

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield KUP

TE Internal #: 1393118-2

General Purpose Power Relay, AC, Monostable, 3 Form C 3PDT-CO, 10 A Contact Rating, 24 VAC Coil Voltage, Potter & Brumfield KUP

[View on TE.com >](#)



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Current Type: **AC**

Coil Magnetic System: **Monostable**

Contact Arrangement: **3 Form C 3PDT-CO**

Contact Current Rating: **10 A**

Features

Product Type Features

|                        |                             |
|------------------------|-----------------------------|
| Relay & Contactor Type | General Purpose Power Relay |
|------------------------|-----------------------------|

Configuration Features

|                         |                            |
|-------------------------|----------------------------|
| Contact Number of Poles | 3                          |
| Coil Special Features   | UL Coil Insulation Class B |
| Contact Arrangement     | 3 Form C 3PDT-CO           |

Electrical Characteristics

|                                                         |             |
|---------------------------------------------------------|-------------|
| Contact Limiting Short-Time Current                     | 10 A        |
| Contact Limiting Making Current                         | 10 A        |
| Contact Limiting Continuous Current                     | 10 A        |
| Contact Limiting Breaking Current                       | 10 A        |
| Insulation Initial Dielectric Between Open Contacts     | 1200 Vrms   |
| Insulation Initial Dielectric Between Adjacent Contacts | 2200 Vrms   |
| Contact Switching Load (Min)                            | 300mA @ 12V |
| Coil Resistance                                         | 72 Ω        |
| Coil Power Rating AC                                    | 2.8 VA      |
| Insulation Initial Resistance                           | 100 MΩ      |
| Contact Current Rating                                  | 10 A        |
| Coil Voltage Rating                                     | 24 VAC      |



|                        |         |
|------------------------|---------|
| Contact Voltage Rating | 240 VAC |
|------------------------|---------|

|                                                       |           |
|-------------------------------------------------------|-----------|
| Insulation Initial Dielectric Between Contacts & Coil | 2200 Vrms |
|-------------------------------------------------------|-----------|

Body Features

|                |                |
|----------------|----------------|
| Product Weight | 85 g[2.988 oz] |
|----------------|----------------|

|                |                |
|----------------|----------------|
| Enclosure Type | Dust Protected |
|----------------|----------------|

Contact Features

|                  |                      |
|------------------|----------------------|
| Contact Material | Silver Cadmium Oxide |
|------------------|----------------------|

Termination Features

|                                    |                         |
|------------------------------------|-------------------------|
| Main Termination & Connection Type | Quick Connect Terminals |
|------------------------------------|-------------------------|

|                                    |                         |
|------------------------------------|-------------------------|
| Coil Termination & Connection Type | Quick Connect Terminals |
|------------------------------------|-------------------------|

Mechanical Attachment

|                               |                            |
|-------------------------------|----------------------------|
| Product Mounting Feature Type | Flange with Mounting Slots |
|-------------------------------|----------------------------|

|                    |                      |
|--------------------|----------------------|
| Product Mount Type | Panel & Socket Mount |
|--------------------|----------------------|

Dimensions

|               |                   |
|---------------|-------------------|
| Product Width | 38.89 mm[1.53 in] |
|---------------|-------------------|

|                |                 |
|----------------|-----------------|
| Product Length | 73.7 mm[2.9 in] |
|----------------|-----------------|

|                |                  |
|----------------|------------------|
| Product Height | 35.71 mm[1.4 in] |
|----------------|------------------|

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -45 – 45 °C[-49 – 113 °F] |
|-----------------------------|---------------------------|

|                                      |     |
|--------------------------------------|-----|
| Environmental Category of Protection | RTI |
|--------------------------------------|-----|

|                                         |               |
|-----------------------------------------|---------------|
| Environmental Ambient Temperature (Max) | 45 °C[113 °F] |
|-----------------------------------------|---------------|

Operation/Application

|              |    |
|--------------|----|
| Current Type | AC |
|--------------|----|

|                      |            |
|----------------------|------------|
| Coil Magnetic System | Monostable |
|----------------------|------------|

Packaging Features

|                  |         |
|------------------|---------|
| Packaging Method | Package |
|------------------|---------|

Other

|                       |      |
|-----------------------|------|
| Contact Current Class | 16 A |
|-----------------------|------|

|                                         |           |
|-----------------------------------------|-----------|
| Environmental Ambient Temperature Class | 0 – 50 °C |
|-----------------------------------------|-----------|

|                           |            |
|---------------------------|------------|
| Height Class (Mechanical) | 30 – 40 mm |
|---------------------------|------------|

|                           |            |
|---------------------------|------------|
| Length Class (Mechanical) | 40 – 50 mm |
|---------------------------|------------|

|  |  |
|--|--|
|  |  |
|--|--|



|                          |            |
|--------------------------|------------|
| Width Class (Mechanical) | 30 – 40 mm |
|--------------------------|------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|-----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>SVHC > Threshold:<br>Cd (7.5% in Component Part)<br>Cadmium oxide (4.37% in 4735210816)<br><b>Article Safe Usage Statements:</b><br>Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                                                                                                                                                                                                                                                                                                                                                                |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                                                                                                                                                                                                                                                                                                                                                                       |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 7-1393117-2  
KUP-14AT5-24=KU



Also in the Series

Potter & Brumfield KUP

AC Relays(31)

General Purpose Power Relays(66)

Relay Accessories(10)

Customers Also Bought

TE Part #2-1393028-8  
OAC-5A = PCB MOUNT, 3A,240V AC - DC I/p

TE Part #CAT-SCH691-SR1B  
Force Guided Relay with 6 contacts

TE Part #745032-1  
9 POS AMPL HSG

TE Part #1609112-8  
10CS1 M0=F7803

TE Part #1617807-6  
FC-335-SY9=RELAY, 3PST

TE Part #1744001-4  
04P MTA156 HDR POL .045SQ TIN

TE Part #6-1393211-0  
T92P7A22-24

TE Part #52927  
PIDG SP SPD 22-16COMM22-18MIL4

TE Part #4-640426-4  
14P MTA156 CONN ASSY 18AWG ORA

Documents

- CAD Files
- Customer View Model
- ENG\_CVM\_CVM\_1393118-2\_D.2d\_dxf.zip
- English
- 3D PDF
- 3D
- Customer View Model



[ENG\\_CVM\\_CVM\\_1393118-2\\_D.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1393118-2\\_D.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KU Sockets & Accessories](#)

English

[KUP Series Panel Plug-in Relay](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English

Agency Approvals

[UL](#)

English