

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel feed-through, for connectors, connection method: Single wires, number of positions: 2+PE, M20, Pin, 450 V, 20 A, PA, gray, coding: P, 2.5 mm<sup>2</sup>, cable length: 0.5 m

## Your advantages

- Easy distribution of power, as components are plugged directly
- Simple, time-saving wiring in the field with Push-Lock connection
- Reliable installation in harsh environments with IP66, IP68, and IP69K throughout the entire system
- Secure, tool-free locking even in particularly difficult installation situations
- Fast commissioning with preassembled cable assemblies

## Commercial data

Item number	1088700
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF6LAB
GTIN	4055626891149
Weight per piece (including packing)	81 g
Weight per piece (excluding packing)	81 g
Customs tariff number	85444290
Country of origin	CN

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## Technical data

### Notes

General	<b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
---------	---

### Product properties

Product family	IPD
Number of positions	3
Connection profile	2+PE
Position marking	L, N, PE
Coding	P

### Insulation characteristics


Overvoltage category	III
Degree of pollution	3

### Connection data

#### Connection technology

Connection method On the device side	Single wires
--------------------------------------	--------------

### Dimensions

Dimensional drawing	
Width	28.5 mm
Height	28.5 mm
Length	43.5 mm

### Electrical properties

Rated surge voltage (III/3)	6 kV
Rated current	20 A (observe derating)
Rated voltage (III/3)	450 V
Nominal voltage $U_N$	450 V AC 450 V DC
Nominal current $I_N$	20 A (observe derating)

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	50 (IP66/IP68/IP69K)
-----------------------------	----------------------

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

	100 (IP66)
--	------------

## Material specifications

Color	light gray (RAL 7035)
Material	PA
Material Seal	EPDM
Contact material	Cu
Contact surface material	Ni/Ag/Sn

## Cable/line

Cable length	0.5 m
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 class 5
Position marking	L, N, PE
Single wire, color	brown, blue, green/yellow
Cable cross section	2.5 mm <sup>2</sup>
Material wire insulation	PVC
Halogen-free	no

## Mounting

Mounting type	Front mounting M20
---------------	--------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66
	IP68 (2 m / 24 h)
	IP69K
	Touch-proof when not plugged in (IP2X)
Impact strength	IK07
Ambient temperature (operation)	-30 °C ... 90 °C
Temperature when conductor connected	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-30 °C ... 90 °C
Resistance to UV radiation	yes

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through




1088700


<https://www.phoenixcontact.com/pc/products/1088700>

## Drawings

Dimensional drawing




Diagram




Derating diagram for 1.0 mm<sup>2</sup>

1088700

<https://www.phoenixcontact.com/pc/products/1088700>



Derating diagram for 1.5 mm<sup>2</sup>



Derating diagram for 2.5 mm<sup>2</sup>

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1088700>



### VDE Zeichengenehmigung

Approval ID: 40059408



### cULus Listed

Approval ID: E468743

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
Only flexible conductors	600 V	20 A	- 14	-
Only rigid conductors	600 V	20 A	- 14	-
multi-stranded with ferrule	600 V	20 A	- 14	-

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## Classifications

### ECLASS

ECLASS-13.0	27440602
ECLASS-15.0	27440602

### ETIM

ETIM 10.0	EC002566
-----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## Mandatory accessories

### IPD PL 3P2,5 F GY - Connector

1088674

<https://www.phoenixcontact.com/pc/products/1088674>



Connector, connection method: Push-lock connection, number of positions: 2+PE, Socket, 0.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, 500 V, 20 A, PA, light gray, coding: P, external cable diameter: 6 mm ... 9 mm and 8 mm ... 13 mm

---

### IPD PL 3P2,5 F A0,5 PVC GY - Connecting cable

1526865

<https://www.phoenixcontact.com/pc/products/1526865>



Connecting cable/ Push-lock connection, number of positions: 2+PE, Socket, 450 V, 16 A, PA, light gray, coding: P, 2.5 mm<sup>2</sup>, cable length: 0.5 m, Socket straight, on free cable end

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## IPD PL 3P2,5 F A1,0 PVC GY - Connecting cable

1526866

<https://www.phoenixcontact.com/pc/products/1526866>



Connecting cable/ Push-lock connection, number of positions: 2+PE, Socket, 450 V, 16 A, PA, light gray, coding: P, 2.5 mm<sup>2</sup>, cable length: 1 m, Socket straight, on free cable end

---

## IPD PL 3P2,5 F A3,0 PVC GY - Connecting cable

1526867

<https://www.phoenixcontact.com/pc/products/1526867>



Connecting cable/ Push-lock connection, number of positions: 2+PE, Socket, 450 V, 16 A, PA, light gray, coding: P, 2.5 mm<sup>2</sup>, cable length: 3 m, Socket straight, on free cable end

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## IPD PL 3P2,5 F A5,0 PVC GY - Connecting cable

1526869

<https://www.phoenixcontact.com/pc/products/1526869>



Connecting cable/ Push-lock connection, number of positions: 2+PE, Socket, 450 V, 16 A, PA, light gray, coding: P, 2.5 mm<sup>2</sup>, cable length: 5 m, Socket straight, on free cable end

---

## IPD PL 3P2,5 M A0,5 F PVC GY - Connecting cable

1526872

<https://www.phoenixcontact.com/pc/products/1526872>



Connecting cable/ Push-lock connection, number of positions: 2+PE, Socket/pin, 450 V, 16 A, PA, light gray, coding: P, 2.5 mm<sup>2</sup>, cable length: 0.5 m, Male straight, on Socket straight

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## IPD PL 3P2,5 M A1,0 F PVC GY - Connecting cable

1526873

<https://www.phoenixcontact.com/pc/products/1526873>



Connecting cable/ Push-lock connection, number of positions: 2+PE, Socket/pin, 450 V, 16 A, PA, light gray, coding: P, 2.5 mm<sup>2</sup>, cable length: 1 m, Male straight, on Socket straight

---

## IPD PL 3P2,5 M A3,0 F PVC GY - Connecting cable

1526874

<https://www.phoenixcontact.com/pc/products/1526874>



Connecting cable/ Push-lock connection, number of positions: 2+PE, Socket/pin, 450 V, 16 A, PA, light gray, coding: P, 2.5 mm<sup>2</sup>, cable length: 3 m, Male straight, on Socket straight

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## IPD PL 3P2,5 M A5,0 F PVC GY - Connecting cable

1526875

<https://www.phoenixcontact.com/pc/products/1526875>



Connecting cable/ Push-lock connection, number of positions: 2+PE, Socket/pin, 450 V, 16 A, PA, light gray, coding: P, 2.5 mm<sup>2</sup>, cable length: 5 m, Male straight, on Socket straight

---

## Accessories

### ZBF 4:UNBEDRUCKT - Zack Marker strip, flat

0808587

<https://www.phoenixcontact.com/pc/products/0808587>



Zack Marker strip, flat, Strip, white, unmarked, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: latching, for terminal block width: 4 mm, Number of individual labels: 10, text field height: 5.2 mm, text field width: 4.2 mm

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## UC-TMF 4 - Marker for terminal blocks

0818166

<https://www.phoenixcontact.com/pc/products/0818166>



Marker for terminal blocks, Sheet, white, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 120, text field height: 5.1 mm, text field width: 3.6 mm

---

## UCT-TMF 4 - Marker for terminal blocks

0828742

<https://www.phoenixcontact.com/pc/products/0828742>



Marker for terminal blocks, Sheet, white, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 90, text field height: 4.7 mm, text field width: 3.4 mm

# IPD W 3P2,5 M 0,5 M20 GY - Panel feed-through



1088700

<https://www.phoenixcontact.com/pc/products/1088700>

## IPD PL CAP W26 WP GY - Protective cap

1088707

<https://www.phoenixcontact.com/pc/products/1088707>



Protective cap, IPD, with locking element, IP66, IP68, IP69K, width: 26 mm, color: gray, for IPD P 3P2,5..., IPD W 3P2,5..., IPD H 3P2,5..., IPD Y 3P2,5

---

## IPD PL COVER W26 YE - Protective cap

1845544

<https://www.phoenixcontact.com/pc/products/1845544>



Protective cap, IPD, IP54, width: 26 mm, color: yellow, for IPD P 3P2,5..., IPD W 3P2,5..., IPD H 3P2,5..., IPD Y 3P2,5

---

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstraße 8  
D-32825 Blomberg  
+49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)