



ENGLISH

Datasheet

IEC Type J PFA Exposed Welded Tip Thermocouples with Miniature

Thermocouple Plug




- Thermocouple type J to IEC 584
- Fast response, welded exposed junction
- Teflon® PFA insulated twin-twisted lead
- Class 1 cable specification in accordance with BS EN 60584-3:2008
- Tolerance to IEC 584 Class 1
- Miniature plug termination
- Temperature range –75°C to +250°C
- Ideal for test & development applications

type	Conductors	Length	Allied code	RS order code
J	1/0.3mm	1m		136-5868
J	1/0.3mm	2m		136-5870
J	1/0.3mm	3m		136-5871
J	1/0.3mm	5m		136-5872
J	1/0.5mm	1m		136-5873
J	1/0.5mm	2m		136-5874
J	1/0.5mm	3m		136-5876
J	1/0.5mm	5m		136-5877
J	1/0.5mm	10m		136-5878

Making your own Thermocouples?

L60 Thermocouple & Fine Wire Welder



The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding

It is primarily designed for use by sensor manufacturers to produce commercial grade thermocouple junctions; it is ideal for producing large numbers of exposed junction thermocouples for test and development laboratories. The L60 Thermocouple Welder is ideally suited to transducer and RTD extension lead attachment

Use of the Thermocouple Welder does not require special skills and most operatives will be capable of producing quality work with little practice. The instrument is supplied with a full range of user accessories including a footswitch

Suitable for use with wires of up to 1.1mm diameter an argon gas shield facility is included but a satisfactory thermocouple junction is produced without the need for argon. The output energy of the L60 Thermocouple Welder can be varied up to 60 Joules

- Simple to use Thermocouple Welder
- Designed for the production of commercial grade thermocouple junctions (See below for range of thermocouple cables)
- Also suitable for other fine wire work
- Front panel or footswitch operation
- Argon gas shield facility

Supplied complete with the following accessories:

- Wire Holding Pliers & Lead
- Safety Glasses
- Magnifying Eyeglass
- Carbon Electrodes
- Spare 2A Fuse
- Argon Hose
- Mains Lead
- Footswitch for greater ease of use



Carbon Electrode

ORDERING INFORMATION

MODELAllied CodeRS ORDER NUMBERFINE WIRE WELDER70825788363-0351Spare Carbon Electrodes (x5) for 1.1mm 250V Fine Wire Welder70656473814-0184

SPECIFICATIONS

General

Energy Output 0-60 Joules Welding Capacity Wires up to 1.1mm diameter Duty Cycle Minimum 5-10 welds/min

MECHANICAL

Physical Dimensions 220mm Wide x 120mm High x 250mm Depth Weight 4kg

ELECTRICAL

Power Supply 110-120 Vac or 220-250 Vac, 50-60Hz Power Consumption Max 170VA dropping to 20VA during charging

MAINTENANCE

Apart from keeping the electrode in good order, no other maintenance is required


(Front View)



(Rear View)



Thermocouple Welder Controls



А	AIC	Argon gas and weld current controlled by the Weld Switch. LED indication
В	Purge	Allows the gas line and electrode shield to be purged of air prior to a new welding period
С	Weld Switch	Initiates a welding operation (in "arc" mode also opens the Argon valve)
D	Argon LED	Indicates when the Argon control valve is open and gas is flowing
E	Wait LED	Glows when weld charge is building
F	Ready LED	"Ready to Weld" indication
G	Power	Rotary control of the capacitor charge voltage
Н	Level Selector	Selects the total capacitance available giving the following values with LED indication


Argan gas and wold current controlled by the "Wold" switch LED indication

"LO" = 0 to 6 Joules "MED" = 0 to 28 Joules "HI" = 0 to 64 Joules

- I Electrode Holder Holds the replaceable carbon electrode which is accessible by removing the outer Argon Shield
- J Red Socket Output socket for using the pliers suppliedK Black Socket Output socket, this provides an additional earth

IEC PTFE Insulated Twin Twisted Pair Thermocouple Cable

Available in Thermocouple Types K, J T & N



Type 'K' Type 'T'

- PTFE twin twisted pair for extending or making simple thermocouples
- Single pair of PTFE insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Suitable for steam & pressure applications, autoclaves, sterilizers etc.
- 25 & 50 metre reel lengths
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour coded to IEC-584-3

T/C Type Conductors Cores Reel Length Allied code RS order code

J	1/0.2mm	+Black/-White	25 metres	70657194	827-5980
J	1/0.2mm	+Black/-White	50 metres	70657195	827-5984
J	1/0.315mm	+Black/-White	25 metres	70657198	827-5993
J	1/0.315mm	+Black/-White	50 metres	70657199	827-5996
K	1/0.315mm	+Green/-White	25 metres	70657200	827-6000
K	1/0.315mm	+Green/-White	50 metres	70657205	827-6019
T	1/0.315mm	+Brown/-White	25 metres	70657208	827-6028
T	1/0.315mm	+Brown/-White	50 metres	70657206	827-6022
J	1/0.508mm	+Black/-White	25 metres	70657197	827-5990
J	1/0.508mm	+Black/-White	50 metres	70657201	827-6003
K	1/0.508mm	+Green/-White	25 metres	70657203	827-6012
K	1/0.508mm	+Green/-White	50 metres	70657204	827-6016
J	7/0.2mm	+Black/-White	25 metres	70657202	827-6006
K	7/0.2mm	+Green/-White	25 metres	70657207	827-6025
T	7/0.2mm	+Brown/-White	25 metres	70657209	827-6031
N	7/0.2mm	+Pink/-White	25 metres	70657210	827-6034

IEC PVC Insulated Flat Pair Thermocouple Extension & Compensating Cable

PVC Insulated Flat Pair (to IEC-584)



- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension types for K, J, T & N
- Compensating types VX (KCB) & U (RCA) for types K & R/S Thermocouples respectively
- Stranded conductors available, either 7/0.2mm or 13/0.2mm
- Available in 10, 25, 100 & 200 metre lengths
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) to IEC-584-3

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Exten	sion:					
KX	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
KX	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
RS232	2/0517					

KX	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
KX	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
JX JX JX	7/0.2mm 7/0.2mm 7/0.2mm 7/0.2mm 7/0.2mm	+Black/-White +Black/-White +Black/-White +Black/-White +Black/-White	Black Black Black Black Black	10 metres 25 metres 50 metres 100 metres 200 metres	70641640 70657078 70657079 70641737 70657081	219-4753 827-5592 827-5596 236-3915 827-5606
TX TX TX TX TX	7/0.2mm 7/0.2mm 7/0.2mm 7/0.2mm 7/0.2mm	+Brown/-White +Brown/-White +Brown/-White +Brown/-White	Brown Brown Brown Brown	10 metres 25 metres 50 metres 100 metres 200 metres	70641637 70641734 70657095 70651749 70657098	219-4703 236-3870 827-5653 762-1146 827-5662
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640

	Conduct				Allied Code	RS order code
Compensating:						
VX (KCB)	7/0.2mn				70657082	827-5609
VX (KCB)	7/0.2mn				70641629	219-4551
VX (KCB)	7/0.2mn				70657080	827-5603
VX (KCB)	7/0.2mn	A			70641630	219-4573
VX (KCB)	7/0.2mn				70657083	827-5612
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	70657086	827-5621
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	70657087	827-5625
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	70657090	827-5634
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	70651750	762-1152
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	70657096	827-5656
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	70646158	611-7902
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	70657097	827-5659
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	70641641	219-4769
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	70657093	827-5643
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	70657094	827-5647


IEC PTFE Single Shot Thermocouple Cable Type K, 10 metre reel

- Thermocouple type K
- 10 metre spool length
- 7/0.2mm diameter conductor
- Operating range: -75°C to +250°C
- Teflon insulated single shot construction
- Resistant to chemicals, oils and fliuds
- Suitable for aerospace applications and is widly used in autoclaves
- Colour coded to IEC-584-3

Туре	Outer	Length	Allied code	RS Code
K	Green/White	10 metres	70657216	827-6053

ANSI PFA Insulated Twin Twisted Pair Thermocouple Cable

Available in Thermocouple Types K & T (ANSI MC96.1)




- PFA Teflon® twin twisted pair for extending or making simple thermocouples
- Single pair of PFA insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam etc.
- Thermocouple types K & T with 1/0.2mm OR 1/0.3 conductors. 7/0.2mm option available for type K
- 25, 50 & 100 metre reel lengths
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour coded to ANSI MC96.1

T/C Type	Conductors	Cores	Reel Length 25 metres 50 metres 100 metres	Allied code	RS order code
KX	1/0.2mm	+Yellow/-Red		70656106	814-0030
KX	1/0.2mm	+Yellow/-Red		70656111	814-0049
KX	1/0.2mm	+Yellow/-Red		70656109	814-0042
KX	7/0.2mm	+Yellow/-Red	25 metres	70656110	814-0046
KX	7/0.2mm	+Yellow/-Red	50 metres	70656113	814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
TX	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
TX	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
TX	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
TX	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
TX	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
TX	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109

ANSI PVC Thermocouple Extension & Compensating Cable

PVC Insulated Flat Pair (ANSI MC96.1)



- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension types for K, J, & T
- Compensating types VX (KCB) for types K Thermocouples
- Stranded conductors available, 7/0.2mm
- Available in 25, 100 & 200 metre lengths
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) to ANSI MC96.1

T/C Type	Conductors	Cores	Jacket	Reel Length	Allied code	RS order code	
Extension:							
KX	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656102	814-0018	
KX	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656105	814-0027	
KX	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656103	814-0020	
JX	7/0.2mm	+ White/-Red	Black	25 m	70656096	813-9995	
JX	7/0.2mm	+ White/-Red	Black	100 m	70656098	814-0005	
JX	7/0.2mm	+ White/-Red	Black	200 m	70656099	814-0008	
TX	7/0.2mm	+Blue/-Red	Blue	25 m	70656119	814-0074	
TX	7/0.2mm	+Blue/-Red	Blue	100 m	70656122	814-0083	
TX	7/0.2mm	+Blue/-Red	Blue	200 m	70656123	814-0086	
Compensating:							
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656127	814-0103	
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656130	814-0112	
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656131	814-0115	