



**06152035**

RCK 15 - Self centring

**2D Technical Drawing**

**Dynamic 3D View**

**Technical Specifications**

|  |          |
|--|----------|
| Part number (CODE)                                   | 06152035 |
| Ød (DD) mm   | 35       |
| ØD (D) mm  | 80       |
| L1 (L1) mm   | 20       |
| L2 (L2) mm   | 25       |
| L3 (L3) mm   | 33       |
| L (L) mm   | 41       |
| Maximum torque Mt (MT) Nm                            | 1260     |
| Clamping pressure - Shaft (CPS) N/mm <sup>2</sup>    | 272      |
| Clamping pressure - Hub (CPH) N/mm <sup>2</sup>      | 120      |
| Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)       | 7        |
| Clamping screws DIN 912 MAT. 12.9 - Type (CST)       | M8x25    |
| Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm | 41       |
| Extraction thread - Type (ETT)                       | M8       |
| Extraction thread - Num. (ETN)                       | 3        |
| Weight (WEIGHT) kg                                   | 1.00     |