

FEATURES

- **Graphite Material:** Provides excellent thermal conductivity and chemical resistance, enhancing durability and performance.
- **Maximum Operating Pressure of 20000 kPa:** Suitable for high-pressure applications, ensuring safety and reliability.
- **Maximum Operating Temperature of 650 °C:** Capable of withstanding extreme temperatures, ideal for high-temperature environments.
- **Rotary Speed of 30 m/s:** Supports high-speed operations, making it versatile for various industrial uses.
- **11mm Section:** Offers a robust and secure fit, ensuring effective sealing.

RS PRO 8m Graphite Gland Packing, 11mm Section

RS Stock No: 606-565



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a high-performance gland packing solution designed for demanding industrial applications. This graphite gland packing is ideal for sealing valves and pumps, providing excellent resistance to high temperatures and pressures, ensuring reliable performance in harsh environments.

General Specifications

Maximum Operating Pressure	20000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	30 m/s
Section	11 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Graphite

Operation Environment Specifications

Maximum Operating Temperature	650 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------