

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect comfort, Type 2, AC charging cable, 32 A Permanent, 480 V AC, with vehicle charging connector and open cable end, cable: 5 m, black, straight, with protective cap, PHOENIX CONTACT logo, IEC 62196-2, for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets

## Product description

AC charging cable with vehicle charging connector and free cable end for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets, for installation at charging stations for e-mobility (EVSE)

## Your advantages

- Complete product range
- Convenient handling due to the ergonomic, triple award-winning design
- Available with your logo on request - for consistent branding of your charging station
- Longitudinal water tightness reliably prevents water ingress
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Tested in accordance with automotive standards LV124, LV214, and LV215-2
- Tested in accordance with EV Ready 37 requirements
- Laser-marked mating face in accordance with DIN EN 17186

## Commercial data

|                                      |                    |
|--------------------------------------|--------------------|
| Item number                          | 1056700            |
| Packing unit                         | 1 pc               |
| Minimum order quantity               | 1 pc               |
| Sales key                            | XWB                |
| Product key                          | XWBAAC             |
| Catalog page                         | Page 21 (C-7-2019) |
| GTIN                                 | 4055626697185      |
| Weight per piece (including packing) | 3,170 g            |
| Weight per piece (excluding packing) | 3,070 g            |
| Customs tariff number                | 85444290           |
| Country of origin                    | PL                 |

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## Technical data

### Product properties

|                     |                                                                                                                                                                          |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product type        | AC charging cable                                                                                                                                                        |
| Product family      | CHARX connect comfort                                                                                                                                                    |
| Application         | for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets<br>for installation at charging stations for electromobility (EVSE) |
| Type                | AC charging cable<br>with vehicle charging connector and open cable end                                                                                                  |
| Design              | with protective cap                                                                                                                                                      |
| Affixed logo        | PHOENIX CONTACT logo                                                                                                                                                     |
| Charging mode       | Mode 3, Case C                                                                                                                                                           |
| Charging standard   | Type 2                                                                                                                                                                   |
| Customer variations | On request                                                                                                                                                               |

### Electrical properties

|                               |                                          |
|-------------------------------|------------------------------------------|
| Type of signal transmission   | Pulse width modulation                   |
| Note on the connection method | Crimp connection, cannot be disconnected |
| Coding                        | 220 $\Omega$ (between PE and PP)         |
| Type of charging current      | AC 3-phase                               |
| Charging power                | 26.6 kW (3-phase)                        |
| Charging current              | 32 A AC (3-phase)                        |

#### Power contact

|               |                       |
|---------------|-----------------------|
| Number        | 5 (L1, L2, L3, N, PE) |
| Rated voltage | 480 V AC              |
| Rated current | 32 A                  |

#### Signal contact

|               |            |
|---------------|------------|
| Number        | 2 (CP, PP) |
| Rated voltage | 30 V AC    |
| Rated current | 2 A        |

## Dimensions

#### Vehicle charging connector

|        |          |
|--------|----------|
| Width  | 70 mm    |
| Height | 137 mm   |
| Depth  | 215.9 mm |

## Material specifications

|                     |              |
|---------------------|--------------|
| Color (Housing)     | black (9005) |
| Color (Handle area) | black (9005) |
| Color (Mating face) | black (9005) |

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

|                                       |              |
|---------------------------------------|--------------|
| Color (Protective cap)                | black (9005) |
| Color (Cable)                         | black (9005) |
| Material (Vehicle charging connector) | Plastic      |
| Material (Cable outer sheath)         | TPE-U        |
| Material (Contact surface)            | Silver       |

## Cable/line

|                                |                                                                         |
|--------------------------------|-------------------------------------------------------------------------|
| Cable length                   | 5 m                                                                     |
| Wiring standards/regulations   | prEN 50620/DIN EN 50620                                                 |
| Wiring certifications          | VDE                                                                     |
| Cable weight                   | max. 505.00 kg/km                                                       |
| Cable type                     | Class 5                                                                 |
| Cable type                     | straight                                                                |
| Cable structure                | 5 x 6.0 mm <sup>2</sup> + 1 x 0.5 mm <sup>2</sup>                       |
| External cable diameter        | 17.00 mm ±0.4 mm                                                        |
| Outer sheath, material         | TPE-U                                                                   |
| Stripping length of the sheath | 70 mm ±5 mm                                                             |
| Stripping length               | 70 mm ±5 mm                                                             |
| Cable resistance               | ≤ 0.0033 Ω/m (based on a power core, at an ambient temperature of 20°C) |
| Bending radius                 | min. 127.5 mm (7.5x diameter)                                           |

## Mechanical properties

### Mechanical data

|                             |         |
|-----------------------------|---------|
| Insertion/withdrawal cycles | > 10000 |
| Insertion force             | < 100 N |
| Withdrawal force            | < 100 N |

## Environmental and real-life conditions

### Ambient conditions

|                                                   |                                                                                                                                                                                                                |
|---------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Degree of protection (Vehicle charging connector) | IP44 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products) |
| Degree of protection (Protective cap)             | IP54                                                                                                                                                                                                           |
| Ambient temperature (operation)                   | -40 °C ... 50 °C                                                                                                                                                                                               |
| Ambient temperature (storage/transport)           | -40 °C ... 80 °C                                                                                                                                                                                               |
| Altitude                                          | 5000 m (above sea level)                                                                                                                                                                                       |

## Standards and regulations

### Standards

|                       |             |
|-----------------------|-------------|
| Standards/regulations | IEC 62196-2 |
|-----------------------|-------------|

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable




1056700

<https://www.phoenixcontact.com/in/products/1056700>


## Drawings

Schematic diagram



### Terminology definition

Dimensional drawing




Make sure that the vehicle charging connector is placed in an appropriate charging connector holder, which ensures a minimum protection rating of IP24 in accordance with IEC 61851-1, for the entire time between charging. To create this charging connector holder, use the dimensions of the vehicle charging connector. Detailed dimensions can also be found in the Download area.

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable

1056700

<https://www.phoenixcontact.com/in/products/1056700>

Schematic diagram



Pin assignment of the Vehicle Connector

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable

1056700

<https://www.phoenixcontact.com/in/products/1056700>

Schematic diagram



Operating instructions

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1056700>

|  | IECEE CB Scheme           |                       |                   |                             |
|-----------------------------------------------------------------------------------|---------------------------|-----------------------|-------------------|-----------------------------|
|                                                                                   | Approval ID: DE1-65898/M1 |                       |                   |                             |
|                                                                                   | Nominal voltage $U_N$     | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                   | 480 V                     | 32 A                  | -                 | -                           |

|  | VDE approval of drawings |                       |                   |                             |
|-----------------------------------------------------------------------------------|--------------------------|-----------------------|-------------------|-----------------------------|
|                                                                                   | Approval ID: 40045387    |                       |                   |                             |
|                                                                                   | Nominal voltage $U_N$    | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                   | 480 V                    | 32 A                  | -                 | -                           |

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27144705 |
| ECLASS-12.0 | 27144705 |
| ECLASS-13.0 | 27144705 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121500 |
|-------------|----------|

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-10                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 4b8bc944-2a1c-48c8-ac85-f39b2dd31864 |

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## Accessories

### EV-T2AC-PARK - Charging connector holder

1624148

<https://www.phoenixcontact.com/in/products/1624148>



CHARX connect, Type 2, Charging connector holder, Accessories, Front mounting, housing: black, for vehicle charging connectors on charging stations (EVSE), PHOENIX CONTACT logo, IEC 62196-2

---

### EV-LABEL-C - Label

1309766

<https://www.phoenixcontact.com/in/products/1309766>



CHARX connect, Label, Accessories, for AC type 2 vehicle charging connector and for AC type 2 vehicle charging inlet, DIN EN 17186

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## CHARX SEC-1000 - AC charging controller

1139034

<https://www.phoenixcontact.com/in/products/1139034>



CHARX control modular, AC charging controller, IEC 61851-1, operating mode: Stand-Alone, Client, interface: CHARX control modular system bus, Connectable peripheral devices: Energy meter, RFID, DC residual current detection, DIN rail mounting

---

## CHARX SEC-3000 - AC charging controller

1139022

<https://www.phoenixcontact.com/in/products/1139022>



CHARX control modular, AC charging controller, with Embedded Linux system, IEC 61851-1, operating mode: Stand-Alone, Client, Server, interface: Ethernet (2 x), CHARX control modular system bus, MICRO-USB type C, communication protocol: OCPP 1.6J, Modbus/TCP, MQTT, Connectable peripheral devices: Energy meter, RFID, DC residual current detection, DIN rail mounting

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## CHARX SEC-3050 - AC charging controller

1139018

<https://www.phoenixcontact.com/in/products/1139018>



CHARX control modular, AC charging controller, with Embedded Linux system, IEC 61851-1, ISO 15118, operating mode: Stand-Alone, Client, Server, interface: Ethernet (2x), CHARX control modular system bus, MICRO-USB type C, communication protocol: OCPP 1.6J, Modbus/TCP, MQTT, Connectable peripheral devices: Energy meter, RFID, DC residual current detection, DIN rail mounting

---

## CHARX SEC-3100 - AC charging controller

1139012

<https://www.phoenixcontact.com/in/products/1139012>



CHARX control modular, AC charging controller, with Embedded Linux system, IEC 61851-1, operating mode: Stand-Alone, Client, Server, interface: Ethernet (2 x), Cellular communication (4G/2G), CHARX control modular system bus, MICRO-USB type C, communication protocol: OCPP 1.6J, Modbus/TCP, MQTT, Connectable peripheral devices: Energy meter, RFID, DC residual current detection, DIN rail mounting

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## CHARX SEC-3150 - AC charging controller

1138965

<https://www.phoenixcontact.com/in/products/1138965>



CHARX control modular, AC charging controller, with Embedded Linux system, IEC 61851-1, ISO 15118, operating mode: Stand-Alone, Client, Server, interface: Ethernet (2x), Cellular communication (4G/2G), CHARX control modular system bus, MICRO-USB type C, communication protocol: OCPP 1.6J, Modbus/TCP, MQTT, Connectable peripheral devices: Energy meter, RFID, DC residual current detection, DIN rail mounting

---

## EEM-EM357 - Measuring device

2908588

<https://www.phoenixcontact.com/in/products/2908588>



3-phase energy meter for active power measurement with direct measurement in grids of up to 500 V/80 A, with S0 output, with digital input and RS-485 interface, certified in accordance with the MID directive

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## EV-CC-AC1-M3-CC-SER-HS - AC charging controller

1622459

<https://www.phoenixcontact.com/in/products/1622459>



The EV-CC-AC1-M3-CBC-SER-HS charging controller with housing for DIN rail mounting is used for charging electric vehicles at 3-phase AC networks according to IEC 61851-1, Mode 3. Optimized for charging stations with permanently mounted Vehicle Connector. All charging functions and comprehensive configuration settings are already integrated.

---

## EV-CC-AC1-M3-CC-SER-PCB - AC charging controller

1622460

<https://www.phoenixcontact.com/in/products/1622460>



The EV-CC-AC1-M3-CC-SER-PCB charging controller as a PCB for charging electric vehicles on a 3-phase AC power grid according to IEC 61851-1, Mode 3. Optimized for charging stations with permanently mounted Vehicle Connector. All charging functions and comprehensive configuration settings are already integrated.

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## EV-CC-AC1-M3-CC-SER-PCB-XC-25X - AC charging controller

1627742

<https://www.phoenixcontact.com/in/products/1627742>



The EV-CC-AC1-M3-CC-SER-PCB charging controller as a PCB for charging electric vehicles on a 3-phase AC power grid according to IEC 61851-1, Mode 3. Optimized for charging stations with permanently mounted Vehicle Connector. All charging functions and comprehensive configuration settings are already integrated.

---

## EV-CC-AC1-M3-CC-SER-PCB-MSTB - AC charging controller

1627367

<https://www.phoenixcontact.com/in/products/1627367>



The EV-CC-AC1-M3-CC-SER-PCB-MSTB charging controller as a PCB for charging electric vehicles according to IEC 61851-1, Mode 3, optimized for charging stations with permanently mounted Vehicle Connector. Connection via PCB connector on header.

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## EM-CP-PP-ETH - AC charging controller

2902802

<https://www.phoenixcontact.com/in/products/2902802>



EV charge control is used to charge electrical vehicles on the 3-phase AC mains power supply according to IEC 61851-1 Mode 3. All necessary control functions are integrated. Additional functions are available for various charging applications.

---

## VAL-EV-T1/T2 264/12.5/3+1 - Lightning/surge arrester type 1/2

1180149

<https://www.phoenixcontact.com/in/products/1180149>



CHARX protect advanced: Plug-in lightning surge/surge protective device, in accordance with Type 1/2 / Class I/II, for 3-phase power supply networks with separate N and PE (5-conductor system: L1, L2, L3, N, PE). Specifically designed for use in e-mobility.

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## VAL-EV-T1/T2 264/12.5/3+1-R - Lightning/surge arrester type 1/2

1180150

<https://www.phoenixcontact.com/in/products/1180150>



CHARX protect advanced: Plug-in lightning surge/surge protective device, in accordance with Type 1/2 / Class I/II, for 3-phase power supply networks with separate N and PE (5-conductor system: L1, L2, L3, N, PE), with remote indication contact. Specifically designed for use in e-mobility.

---

## VAL-EV-T2 280/3+1 - Type 2 surge arrester

1180144

<https://www.phoenixcontact.com/in/products/1180144>



CHARX protect basic: Plug-in surge protective device, in accordance with Type 2/Class II, for 3-phase power supply networks with separate N and PE (5-conductor system: L1, L2, L3, N, PE). Specifically designed for use in e-mobility.

# EV-T2G3C-3AC32A-5,0M6,0ESBK11 - AC charging cable



1056700

<https://www.phoenixcontact.com/in/products/1056700>

## VAL-EV-T2 280/3+1-R - Type 2 surge arrester

1180145

<https://www.phoenixcontact.com/in/products/1180145>



CHARX protect basic: Plug-in surge protective device, in accordance with Type 2/Class II, for 3-phase power supply networks with separate N and PE (5-conductor system: L1, L2, L3, N, PE), with remote indication contact. Specifically designed for use in e-mobility.

---

## G-INS-M32-M68N-PNES-BK - Cable gland

1411136

<https://www.phoenixcontact.com/in/products/1411136>



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 15 mm ... 21 mm, shielding: no, connecting thread: M32 x 1.5, color: jet black RAL 9005

---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)