

230 V / 950 WATTS, 65%RF CR130, 13051.0-02,



Model		
product brand name	SIVACON	
product designation	heater unit	
design of the product	With integrated hygrostat	
General technical data		
consumed active power rated value	950 W	
Voltage		
type of voltage of the operating voltage	AC	
continuous heating power at 20 °C	950 W	
operating voltage		
<ul style="list-style-type: none"> rated value minimum rated value maximum at AC at 50 Hz rated value minimum at AC at 50 Hz rated value maximum at AC at 60 Hz rated value minimum at AC at 60 Hz rated value maximum 	230 V 230 V 230 V 230 V 230 V 230 V	
Protection class		
protection class IP	IP20	
Main circuit		
operational current of the slow-blow fuse link	8 A	
Product details		
product component		
<ul style="list-style-type: none"> blower thermostat 	Yes Yes	
Connections		
tightening torque with screw-type terminals maximum	0.8 N·m	
type of connection technology	2-pole terminal 2.5 mm ² with strain relief	
Mechanical Design		
height	182 mm	
width	160 mm	
depth	99 mm	
fastening method	Clip for 35 mm DIN rail or screw mounting M6	
mounting position	air flow direction vertical (air outlet on top)	
net weight	1.5 kg	
material of the enclosure	plastic	
Environmental conditions		
relative humidity reference value	90 %	
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2150-0CA>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2150-0CA>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2150-0CA

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025

