

# Product datasheet

Specifications



## TeSys K reversing contactor - 3P - AC-3 $\leq$ 440 V 6 A - 1 NC - 220...230 VAC coil

Local distributor code:

398354060

LC2K0601M7

EAN Code: 3389110429428

## Main

Range	TeSys
Product name	TeSys K
Product or component type	Reversing contactor
Device short name	LC2K
Device application	Control
Contact application	Motor control
Utilisation category	AC-3 AC-3e AC-4
Device presentation	Preassembled with reversing power busbar
Poles description	3P
power pole contact composition	3 NO
[Ue] rated operational voltage	Power circuit: 690 V AC 50/60 Hz Signalling circuit: $\leq$ 690 V AC 50/60 Hz
[Ie] rated operational current	6 A (at $\leq$ 60 °C) at $\leq$ 440 V AC AC-3 for power circuit 6 A (at $\leq$ 60 °C) at $\leq$ 440 V AC AC-3e for power circuit
Motor power kW	1.5 kW at 220...230 V AC 50/60 Hz 2.2 kW at 380...415 V AC 50/60 Hz 3 kW at 440/690 V AC 50/60 Hz
Control circuit type	AC at 50/60 Hz
[Uc] control circuit voltage	220...230 V AC 50/60 Hz
Auxiliary contact composition	1 NC
[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	20 A (at 60 °C) for power circuit 10 A (at 50 °C) for signalling circuit
Irms rated making capacity	110 A AC for power circuit conforming to IEC 60947 110 A AC for signalling circuit conforming to IEC 60947
Rated breaking capacity	110 A at 220...230 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947

<b>[Icw] rated short-time withstand current</b>	<p>90 A 50 °C - 1 s for power circuit  85 A 50 °C - 5 s for power circuit  80 A 50 °C - 10 s for power circuit  60 A 50 °C - 30 s for power circuit  45 A 50 °C - 1 min for power circuit  40 A 50 °C - 3 min for power circuit  20 A 50 °C - &gt;= 15 min for power circuit  80 A - 1 s for signalling circuit  90 A - 500 ms for signalling circuit  110 A - 100 ms for signalling circuit</p>
<b>Associated fuse rating</b>	<p>25 A gG at &lt;= 440 V for power circuit  25 A aM for power circuit  10 A gG for signalling circuit conforming to IEC 60947  10 A gG for signalling circuit conforming to VDE 0660</p>
<b>Average impedance</b>	3 mOhm - lth 20 A 50 Hz for power circuit
<b>[Ui] rated insulation voltage</b>	<p>Power circuit: 600 V conforming to UL 508  Power circuit: 690 V conforming to IEC 60947-4-1  Signalling circuit: 690 V conforming to IEC 60947-4-1  Signalling circuit: 690 V conforming to IEC 60947-5-1  Signalling circuit: 600 V conforming to UL 508  Power circuit: 600 V conforming to CSA C22.2 No 14  Signalling circuit: 600 V conforming to CSA C22.2 No 14</p>
<b>Electrical durability</b>	<p>1.3 Mcycles 6 A AC-3 at Ue &lt;= 440 V  1.3 Mcycles 6 A AC-3e at Ue &lt;= 440 V  0.05 Mcycles 36 A AC-4 at Ue &lt;= 440 V</p>
<b>Interlocking type</b>	Mechanical
<b>Mounting support</b>	<p>Plate  Rail</p>
<b>Standards</b>	<p>EN/IEC 60947-4-1  GB/T 14048.4  UL 60947-4-1  CSA C22.2 No 60947-4-1  JIS C8201-4-1</p>
<b>Product certifications</b>	<p>CB Scheme  CCC  UL  CSA  EAC  CE  UKCA</p>
<b>Connections - terminals</b>	<p>Screw clamp terminals 1 cable(s) 1.5...4 mm<sup>2</sup>solid  Screw clamp terminals 1 cable(s) 0.75...4 mm<sup>2</sup>flexible without cable end  Screw clamp terminals 1 cable(s) 0.34...2.5 mm<sup>2</sup>flexible with cable end  Screw clamp terminals 2 cable(s) 1.5...4 mm<sup>2</sup>solid  Screw clamp terminals 2 cable(s) 0.75...4 mm<sup>2</sup>flexible without cable end  Screw clamp terminals 2 cable(s) 0.34...1.5 mm<sup>2</sup>flexible with cable end</p>
<b>Tightening torque</b>	<p>0.8...1.3 N.m - on screw clamp terminals Philips No 2  0.8...1.3 N.m - on screw clamp terminals flat Ø 6 mm  0.8...1.3 N.m - on screw clamp terminals pozidriv No 2</p>
<b>Operating time</b>	<p>10...20 ms coil energisation and NO closing  10...20 ms coil de-energisation and NO opening</p>
<b>Safety reliability level</b>	<p>B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1  B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1</p>
<b>Mechanical durability</b>	5 Mcycles
<b>Maximum operating rate</b>	3600 cyc/h
<b>Complementary</b>	
<b>Control circuit voltage limits</b>	<p>Operational: 0.8...1.15 Uc (at &lt;50 °C)  Drop-out: 0.2...0.75 Uc (at &lt;50 °C)</p>
<b>Inrush power in VA</b>	30 VA (at 20 °C)

<b>Hold-in power consumption in VA</b>	4.5 VA (at 20 °C)
<b>Heat dissipation</b>	1.3 W
<b>Auxiliary contacts type</b>	type instantaneous 1 NC
<b>Signalling circuit frequency</b>	<= 400 Hz
<b>Minimum switching current</b>	5 mA for signalling circuit
<b>Minimum switching voltage</b>	17 V for signalling circuit
<b>Non overlap distance</b>	0.5 mm
<b>Insulation resistance</b>	> 10 MOhm for signalling circuit

## Environment

<b>IP degree of protection</b>	IP20 conforming to VDE 0106
<b>Protective treatment</b>	TC conforming to IEC 60068 TC conforming to DIN 50016
<b>Ambient air temperature for operation</b>	-25...50 °C
<b>Ambient air temperature for storage</b>	-50...80 °C
<b>Operating altitude</b>	2000 m without derating
<b>Flame retardance</b>	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
<b>Mechanical robustness</b>	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5...300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6
<b>Height</b>	58 mm
<b>Width</b>	90 mm
<b>Depth</b>	57 mm
<b>Net weight</b>	0.39 kg

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	6.5 cm
<b>Package 1 Width</b>	6.0 cm
<b>Package 1 Length</b>	9.2 cm
<b>Package 1 Weight</b>	363.0 g
<b>Unit Type of Package 2</b>	S02
<b>Number of Units in Package 2</b>	25
<b>Package 2 Height</b>	15.0 cm
<b>Package 2 Width</b>	30.0 cm
<b>Package 2 Length</b>	40.0 cm
<b>Package 2 Weight</b>	9.417 kg

## Logistical informations

---

Country of origin FR

## Contractual warranty

---

Warranty (in months) 18



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint 101

Environmental Disclosure [Product Environmental Profile](#)

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant

REACH Regulation [REACH Declaration](#)

### Use Longer

#### Lifetime extension

Repair No

### Use Again

#### Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back No


WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings


Dimensions

---

Reversing Contactors LC2 K, LP2 K, LP5 K: Mounting on Panel



Reversing Contactors LC2 K, LP2 K, LP5 K: Mounting on Rail AM1 DP200 or AM1 DE200 (35 mm)




Connections and Schema


Wiring

---

3-Pole Reversing Contactors with Screw Clamp Connections: 3P + N/O



3-Pole Reversing Contactors with Screw Clamp Connections: 3P + N/C



Offer Marketing Illustration

Product benefits / Features

---

## TeSys K Technical Benefits



- Preassembled with reversing power busbar
- Built-in in all 3 pole versions: 1NO or 1NC
- Up to 4 more by add-on blocks
- Wide variety of coil voltage and terminal connection options
- Delivers strong performance for its compact size and promises seamless integration in all applications and use
- Pre-wired power circuit connections as standard on screw clamp versions.
- It Features specific versions for railway (TeSys S207) and electrodomestic (TeSys S335) applications

Offer Marketing Illustration

Product benefits / Features

---

## TeSys K

### Reversing contactors



#### Flexibility

Designed with control voltages, low consumption, minimal noise levels, robust power connections, and a range of auxiliaries, and application-specific variants to meet diverse needs.



#### Safety

It provide ultimate protection with IP20 finger-safe terminals, built-in NO/NC auxiliary contacts, and IEC-certified mirror and mechanically linked contacts for safety applications.



#### Compact size

Up to 50% less volume is captured in your panels. One of the smallest contactors offerings in the market



Technical Illustration

Assembly's dimensions

---

