

SHOWA

7502PF

DISPOSABLE PROTECTION

Biodegradable, chemical resistant and powder free disposable glove with no accelerator


This bio-degradable and powder free glove is also made without accelerators found in regular nitrile gloves which reduces the chances of skin irritation in those with allergies or sensitive skin. However it still provides the same

Features

- ▲ 100% nitrile disposable glove with textured fingertips
- ▲ Engineered with Eco Best Technology, making the glove biodegradable in biologically active landfills
- ▲ Non-sterile, silicone and latex free
- ▲ Accelerator-free formulation protects very sensitive skin
- ▲ Protects from a wide array of chemical hazards while avoiding type and type IV latex allergies
- ▲ Low-modulus formulation to improve fit and reduce fatigue
- ▲ Ambidextrous aiding the ability to easily put on and remove
- ▲ AQL 1.5



Certifications



Suitable industries & applications

Industries

- ▲ Food Production
- ▲ Automotive
- ▲ Healthcare
- ▲ Education and Research
- ▲ Manufacturing
- ▲ Chemicals
- ▲ Highways and Infrastructure

Applications

- ▲ Component and Product Assembly
- ▲ Vehicle Repairs and Maintenance
- ▲ Chemical Handling and Containment
- ▲ Food Preparation and Handling
- ▲ Laboratory Analysis

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

 **GLOBUS**

SHOWA 7502PF

DISPOSABLE PROTECTION

Biodegradable, chemical resistant and powder free disposable glove with no accelerator

Product information

Materials	Liner:	Unlined/Unsupported
	Coating:	Nitrile
Colour	Blue	
Cuff Style	Beaded	

Ordering information

XS	SHO75020	Items per Pack 1 x Box of 200 *
S	SHO75021	
M	SHO75022	
L	SHO75023	Items per Case 10 x Box of 200 *
XL	SHO75024	
XXL	SHO75025	

* NB. XXL = Box of 180

Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.

 **GLOBUS**