



**FAG****X-life****7313-B-XL-MP-UA**

Angular contact ball bearing

Angular contact ball bearing 73...-B-XL-MP,
single row, X-life, solid brass cage

Technical information



Your current product variant

Design variant	B	B
Sealing	Without	Not sealed
Cage	MP	solid brass cage, ball guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Bearing with matched conditions for fitting in pairs	UA	bearing set with small axial internal clearance
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	65 mm	Bore diameter
D	140 mm	Outside diameter
B	33 mm	Width
C _r	110,000 N	Basic dynamic load rating, radial
C _{0r}	82,000 N	Basic static load rating, radial
C _{ur}	5,600 N	Fatigue load limit, radial
n _G	8,400 1/min	Limiting speed
n _{gr}	5,000 1/min	Reference speed
m	2.355 kg	Weight



Mounting dimensions

$d_{a\ min}$	77 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	128 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	133 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2.1 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	1 mm	Maximum fillet radius of housing

Dimensions

$r_{\ min}$	2.1 mm	Minimum chamfer dimension
$r_{1\ min}$	1.1 mm	Minimum chamfer dimension
D_1	111.52 mm	Shoulder diameter on outer ring wide side face
d_1	95.3 mm	Shoulder diameter on inner ring wide side face
a	59.5 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	150 °C	Operating temperature max.


Additional information

$A_{\ min}$	46 µm	Axial clearance per set min.
Tol (+)	12 µm	Tolerance for axial clearance or preload per set

Characteristics



Radial load



Axial load in one direction



Grease Lubrication



Oil Lubrication



Not sealed