



**Part Number :** [347730142](#)

**Product Description :** Stac64 Hybrid Header, 14 Circuits, Right-Angle, Polarization C, Mylar Pin Alignment Plate, Brown, Tray

**Series Number :** 34773

**Status :** Active

**Product Category :** PCB Headers and Receptacles

**Packaging Alternative :** [347739142](#) (Tube)



---

## Documents & Resources

### Drawings

[347730142\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications


[347290200-AS-CH-000.pdf](#)

[PS-34969-100-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Boric acid per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	PCB Headers and Receptacles
Series	34773
Description	Stac64 Hybrid Header, 14 Circuits, Right-Angle, Polarization C, Mylar Pin Alignment Plate, Brown, Tray
Application	Automotive, Power, Wire-to-Board
Comments	Current is dependent on connector size, ambient temperature, blade size and related factors. 2.80mm - 30.0A; 0.64mm - 6.0A; Polarization C
Component Type	PCB Header
Product Name	Stac64
UPC	884982910546

### Electrical

Current - Maximum per Contact	30.0A, 6.0A
Voltage - Maximum	500V DC

### Physical

Breakaway	No
-----------	----

Circuits Detail	10 x 0.64 and 4 x 2.8
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Brown
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	9.600/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Pitch - Mating Interface	2.54mm, 5.25mm
Pitch - Termination Interface	2.54mm, 5.25mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

### Solder Process Data

Max-Duration	40
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	260

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Stac64 Hybrid Receptacle Assemblies	<u>34969</u>

---

This document was generated on Sep 23, 2025