




Part Number : [2239362100](#)
Product Description : 1.00mm Pitch, Rely-On
Receptacle Crimp Housing, Single Row, Inner Positive
Lock, 10 Circuits, Black
Series Number : 223936
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

- [2239362100 sd.pdf](#)
- [2239369200-SPK-200.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [2239360000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	223936
Description	1.00mm Pitch, Rely-On Receptacle Crimp Housing, Single Row, Inner Positive Lock, 10 Circuits, Black
Application	Wire-to-Board
Component Type	Housing
Product Name	Rely-On
UPC	198282573623

Physical

Circuits (maximum)	10
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polyamide (PA)
Net Weight	147.180/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Rely-On 1.0 Verticle Single Row Inner Positive Lock Headers	<u>223938</u>
Rely-On 1.0 Right-Angle Single Row Inner Positive Lock Headers	<u>223939</u>

Use with Part(s)

Description	Part Number
Rely-On 1.0 Female Crimp Terminals	<u>223937</u>