

230 V / 950WATTS, 0-60DEGR. CR130, 13051.0-00,



Model	
product brand name	SIVACON
product designation	heater unit
design of the product	With integrated thermostat
General technical data	
consumed active power rated value	950 W
Voltage	
type of voltage of the operating voltage	AC
continuous heating power at 20 °C	950 W
operating voltage	
<ul style="list-style-type: none"> rated value minimum rated value maximum at AC at 50 Hz rated value minimum at AC at 50 Hz rated value maximum at AC at 60 Hz rated value minimum at AC at 60 Hz rated value maximum 	230 V 230 V 230 V 230 V 230 V 230 V
Protection class	
protection class IP	IP20
Main circuit	
operational current of the slow-blow fuse link	8 A
Adjustable parameters	
adjustable temperature	
<ul style="list-style-type: none"> initial value full-scale value 	0 °C 60 °C
Product details	
product component	
<ul style="list-style-type: none"> blower thermostat 	Yes Yes
Connections	
tightening torque with screw-type terminals maximum	0.8 N·m
type of connection technology	2-pole terminal 2.5 mm ² with strain relief
Mechanical Design	
height	182 mm
width	160 mm
depth	99 mm
fastening method	Clip for 35 mm DIN rail or screw mounting M6
mounting position	air flow direction vertical (air outlet on top)
net weight	1.5 kg
material of the enclosure	plastic
Environmental conditions	

relative humidity reference value

90 %

Approvals Certificates

General Product Approval

other

Environment



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2150-0C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2150-0C>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2150-0C

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025

