

Technical data



2302S

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	15 mm
D - External diameter	42 mm
B - Bearing/Inner ring width	17 mm
rs - Min fillet radius	1 mm
Radial clearance class	CN
Precision class	P0
Mass	0,113 kg

PRODUCT PERFORMANCE

C - Dynamic load	12300000 mN
C0 - Static load	2910000 mN
Cu - Fatigue limit load	130000 mN
e - Coefficient	0.51
Y0 - Static axial load coefficient	1.3
Y1 - Lower axial load coefficient	1.2
Y2 - Upper axial load coefficient	1.9
N lim - Oil lubrication limit speed	108000 °/s
N lim - Grease lubrication limit speed	84000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	20 mm
Da max - Max shoulder diameter OR	37 mm



2302S
Double-row self-aligning ball bearings

ABUTMENT	
ra max - Max shaft & housing fillet radius	1 mm