


Castor D75 swivel with double-brake



The D75 castor series (castor diameter 75 mm) has a robust metal housing and a castor that can support a load of 60 kg. As swivel castors or swivel castors with double brake, the castors are attached via the end face in the core boring of a profile or via a base plate.



Scope of Delivery

Steel sheet casing bright zinc-plated, black
Swivelling axis with sealed ball bearing,
Wheel axle with sealed ball bearing,
Dust shield,
Tyre TPE, track-free, 80 Sh A, grey

Technical note

[0.0.420.16](#) For more information, please click here!

Properties	
Article number	0.0.420.16
Delivery unit	1 pce.
Weight	340.0 g
Load-carrying capacity	60 kg/Castor

Accessoires