




TE Internal #: 2479976-7
SMA Cable Assembly, 3.048 m [10 ft], Blue Cable, 0 – 18 GHz
Operating Frequency, 50 ohm, FEP, 2.64 mm [.104 in] Diameter,
SMA Plug End A
[View on TE.com >](#)

Cable Assemblies > RF Cable Assemblies



Cable Assembly (End A): **SMA Plug**
Cable Assembly (End B): **SMA Plug**
Cable Assembly Length: **3.048 m [10 ft]**
Coax Cable Type: **RG 405SS**
Impedance: **50 Ω**

Features

Product Type Features

Cable Assembly (End A)	SMA Plug
Cable Assembly (End B)	SMA Plug
Coax Cable Type	RG 405SS
Cable Assembly Type	SMA

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Operating Voltage	335 VAC
Impedance	50 Ω

Body Features

Jacket Material	FEP
Cable Color	Blue

Contact Features

Center Contact Plating	Gold
------------------------	------



Contact Base Material

Brass

Dimensions

Outside Cable Diameter

2.64 mm[.104 in]

Usage Conditions

Operating Temperature Range

-45 – 125 °C[-49 – 257 °F]

Operation/Application

Operating Frequency

0 – 18 GHz

Other

Dielectric Material

PTFE

Cable Assembly Length

3.048 m[10 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
SVHC > Threshold:
Pb (3.34% in Component Part)
Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An



Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 5-1814400-2
SMA R/A PCB Skt GZD



TE Part # 5-1814832-2
SMA Str PCB Skt GZD

Documents

Product Drawings

SMA M to SMA M Str 18G Flexible.086 120"

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2479976-7_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2479976-7_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2479976-7_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

dnd-fly-RF-cable-assemblies-product-expansion

English

Product Specifications

Product Specification

English