

HRIG-POA 72G

Levelling castor, with integrated truck lock and bolt hole, nylon wheel

EAN 4047526117535

ID 757014

Customs tariff number 83022000

Bracket: HRIG series

- die-cast aluminium, powder-coated, colour ivory
- sealed ball bearing in the swivel head
- hexagonal steel top plate
- female thread in bolt hole
- truck lock made of hard rubber
- height adjustment using wrench or integrated adjustment wheel
- steel parts zinc-plated, blue-passivated, Cr6-free

Wheel: POA series

- high-quality nylon 6, impact resistant, hardness 70 Shore D, colour black

Other features:

- Load capacity determined under the following conditions:
 - speed: max. 1 km/h
 - temperature: +15 °C to +30 °C
 - hardness, horizontal tread without obstacles
 - route: A cooling off period of 15 minutes is required after a maximum of 50 m

Technical data:

Wheel Ø (D)	⌀	72 mm
Wheel width	∅	32 mm
Load capacity at 1 km/h	⬆	750 kg
Static load capacity when stable and locked		800 kg
Bearing type	⊙	plain bore
Total height (H)	⊘	120 mm
Max. total height (h)	⊘	132 mm
Mounting type		female thread
Adjustment range (T4)	↕	12 mm
Inner thread		M16 x 16 mm
Offset (F)	⊘	52 mm
Temperature resistance min		-10 °C
Temperature resistance max		80 °C
Tread and tyre hardness		70 Shore D
Unit weight	⚖	1.7 kg
Non-marking		✓
Non-staining		✓
Antistatic	⚡	✗
Electrically conductive	⚡	✗
Corrosion-resistant		✗
Heat-resistant	🔥	✗
Suitable for autoclaves		✗



Tread and tyre hardness

■■■■■ 70 Shore D

Rolling resistance


■■■■■ excellent

Wear resistance

■■■■□ good

Operating noise / floor surface preservation

■■■■□ satisfactory



Suitable for machine washing	×
------------------------------	---