


Features

- Steel wire armoured
- Suitable for direct burial
- BS5467

RS PRO Power Cable

RS Stock No.: 196-4655



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Power Cable



Product Description

Manufactured to BS 5467 Table 6 (2 Core) Table 8 (3 Core) Table 10 (4 Core) Table 13 (5 Core).

Plain Annealed Copper Conductor / XLPE Insulated / PVC Bedded / Galvanised Steel Wire Armour / PVC Sheathed. 600/1000V

Steel Wire Armoured cables are predominantly used for industrial wiring and mains distribution. They are designed to be used in industrial areas , in and around buildings and other similar environments.

These cables are designed to be installed in air, clipped to surface, on cable tray/ladder work, embedded in concrete and buried direct or in ducting underground

General Specifications

Conductor	16.0sqmm class 2 stranded plain annealed copper
Insulation Material	XLPE
Insulation Colour	Blue, Brown, Black, Grey
Bedding Material	Polymeric compound
Armouring	Galvanised Steel Wire
Sheath Material	PVC (Type 9)
Sheath Colour	Black
Approximate Diameter	22.8mm
Number of conductors	4
Reel length	100 metres

Mechanical Specifications

Minimum temperature	-15°C
Maximum temperature	+90°C

Electrical Specifications

Voltage rating	600/1000V	
Current rating	See Table 4E4A of BS7671	

Approvals

Declarations	MFR Declaration of Conformity	
Third Party Approvals	British Approvals Service for Cables (BASEC)	
Standards Met	BS5467	

Power Cable



Similar Products

Stock No.	Brand	Number of Conductors	Conductor Size (mm²)	Armouring	Colour	Reel length
		conductors	0.20 ()			(m)
406466	56.556		4 =	Galvanised Steel	5	
1964667	RS PRO	2	1.5	Wire	Black	50
4064650	DC DDO	2	4.5	Galvanised Steel	Disal	400
1964658	RS PRO	2	1.5	Wire Galvanised Steel	Black	100
1964662	RS PRO	2	2.5	Wire	Black	50
1904002	KSFKO	2	2.5	VVIIE	Diack	30
				Galvanised Steel		
1964720	RS PRO	3	1.5	Wire	Black	50
				Galvanised Steel	2.0.0.1	
1964709	RS PRO	3	1.5	Wire	Black	100
				Galvanised Steel		
1964715	RS PRO	3	2.5	Wire	Black	50
				Galvanised Steel		
1964718	RS PRO	3	2.5	Wire	Black	100
				Galvanised Steel		
1964707	RS PRO	3	4.0	Wire	Black	50
				Galvanised Steel		
1964681	RS PRO	3	4.0	Wire	Black	100
				Galvanised Steel		
1964708	RS PRO	3	6.0	Wire	Black	50
				Galvanised Steel		
1964690	RS PRO	3	10.0	Wire	Black	50
1051500			4 =	Galvanised Steel	5	
1964699	RS PRO	4	1.5	Wire	Black	50
1064600		4	1.5	Galvanised Steel	Dlask	100
1964698	RS PRO	4	1.5	Wire	Black	100
1964711	RS PRO	4	2.5	Galvanised Steel Wire	Black	50
1304711	KSFKO	4	2.5	Galvanised Steel	Diack	30
1964673	RS PRO	4	2.5	Wire	Black	100
1304073	KSTKO		2.3	Galvanised Steel	Black	100
1964694	RS PRO	4	4.0	Wire	Black	50
1301031	NO I NO			Galvanised Steel	2.deit	30
1964687	RS PRO	4	4.0	Wire	Black	100
			-	Galvanised Steel		-
1964688	RS PRO	4	6.0	Wire	Black	50
				Galvanised Steel		
1964705	RS PRO	4	6.0	Wire	Black	100
				Galvanised Steel		
1964706	RS PRO	4	10.0	Wire	Black	50

Power Cable



				Galvanised Steel		
1964671	RS PRO	4	16.0	Wire	Black	50
				Galvanised Steel		
1964655	RS PRO	4	16.0	Wire	Black	100
				Galvanised Steel		
1964697	RS PRO	5	2.5	Wire	Black	50
				Galvanised Steel		
1964700	RS PRO	5	4.0	Wire	Black	50