





ITV00**, Compact Electro-Pneumatic Regulator

ITV0050-3BL

Datasheet

- Built-in one-touch fitting
- Error indication LED
- High stability
- High-response time
- Compact and lightweight








Electro-pneumatic regulator

Standard specifications

Pressure Range	5 (0.001 to 0.9 MPa)
Power Voltage	0 (DC24V)
Input Signal	3 (Voltage Style 0~10 V DC)
Built-in One-touch Fitting	Metric Size One-touch Fitting
Base Type	Single Unit [Standard Base Type]
Bracket	B (Flat Bracket for Standard Base Type)
Cable Connector	L (Right Angle Style 3 M)
Maximum operating pressure	1.0 MPa
Minimum operating pressure	0.1 MPa
General power supply	24 V DC $\pm 10\%$, max. 0.12 A
Conform to the European RoHS Directive	Conform
Approvals	CE
Pneumatic input connection	Ø 4 mm
Pneumatic output connection	Ø 4 mm
Pneumatic exhaust connection	Ø 4 mm
Flow rate of secondary exhaust	6.0 Nl/min
Maximum output pressure	0.9 MPa
Current consumption	0.12 A
Enclosure	IP65

Sensitivity	Within 0.2% (Full span)
Repeatability	Within $\pm 0.5\%$ (Full span)
Set pressure range	0.001 - 0.1 MPa
Linearity	Within $\pm 1\%$ (Full span)
Power supply voltage	24 VDC $\pm 10\%$
Max. supply pressure	1.0 MPa
Min. supply pressure	Set pressure +0.1 MPa
Temperature characteristics	Within $\pm 0.12\%$ (Full span)/°C
Connection	Built-in One-touch fittings
Hysteresis	Within 0.5% (Full span)
Input signal Voltage type	0 - 10 VDC
Input impedance Voltage type	10 k Ω
Output signal Analogue	1 to 5 VDC (Output impedance: Approximately 1 k Ω) Output accuracy within $\pm 6\%$ (Full span)
Weight	0.160 Kg



Additional information

Catalogue	ITV-Ff_EU.pdf
Declaration of conformity	newDoC_ITV0000_TF1V091EN.pdf newDoC_ITV0000_TF1Y245EN.pdf DoC_ITV00x_TF00001-B.pdf
Installation manuals	IMM_ITV00x_TF110GB-A.pdf
Operation manuals	OM_ITV0_OM00002EN.pdf itv0000_op_man_itv0-om00002.pdf