

UCT-WMTBA (40X17) - Cable marker



1014086

<https://www.phoenixcontact.com/gb/products/1014086>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, BLUEMARK E.CARD, THERMOMARK PRIME 2.0, mounting type: Assembly with cable ties, cable diameter: > 6 mm, Number of individual labels: 3, text field height: 17 mm, text field width: 40 mm

Your advantages

- The UCT-WMTBA ... UniCard labeling range includes markers that can be secured using standard cable binders
- Thanks to their angular shape the markers fit perfectly onto cables
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	1014086
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2318
Product key	BG2318
Catalog page	Page 210 (C-3-2019)
GTIN	4046356781381
Weight per piece (including packing)	9.62 g
Weight per piece (excluding packing)	9.62 g
Customs tariff number	39269097
Country of origin	PL

UCT-WMTBA (40X17) - Cable marker



1014086

<https://www.phoenixcontact.com/gb/products/1014086>

Technical data

Product properties

Product type	Conductor marking
Type	Card form

Marking

Number of individual labels	3
Number of individual labels per row	1

Dimensions

Width	17 mm
Length	40 mm

External dimensions

Outside diameter	> 6 mm ... 136 mm
------------------	-------------------

Text field

Text field width	40 mm
Text field height	17 mm

Material specifications

Color	white (RAL 9010)
Material	PC
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	> 6.00 mm
-------------------------	-----------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

UCT-WMTBA (40X17) - Cable marker



1014086

<https://www.phoenixcontact.com/gb/products/1014086>

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UCT-WMTBA (40X17) - Cable marker



1014086

<https://www.phoenixcontact.com/gb/products/1014086>

Shelf life	2 years
------------	---------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

UCT-WMTBA (40X17) - Cable marker



1014086

<https://www.phoenixcontact.com/gb/products/1014086>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT-WMTBA (40X17) - Cable marker



1014086
<https://www.phoenixcontact.com/gb/products/1014086>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.041 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk