

Polisher XGT®

PV001G

40Vmax • 180 mm • 0 - 2 200 min⁻¹

XGT® Battery powered Polisher for professionals.

Makita's PV001G for polishing cars, boats and other solid surfaces. Powerful Brushless motor is electronically controlled to optimize battery energy use for longer run time per charge. Constant speed control maintains constant speed under load, critical for a professional finish.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	600 – 2200 min ⁻¹
Continuous use XGT® 40Vmax / 2.5 Ah	9 - 42 min
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Sound Power Level (L _{WA})	91 dB(A)
Sound Pressure Level (L _{pA})	83 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Uncertainty (K Factor)	1,5 m/s ²
Spindle Thread	M14
Vibration Level (3 axes), Polishing	≤ 2,5 m/s ²
Tool weight with battery	3,0 - 4,4 kg
Product net weight	2,3 kg

User benefits

- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Soft start for smooth start-ups
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing