



Expertise – Passion – Automation



Your safety in our focus

Safety-related products


5 port valve with spool position detection

SY-X30 Series

5 port valve with spool position detection

SY-X30 Series

- ▶ We focus on machinery safety as a key part of our product development strategy. This version will help satisfy your machine safety system requirements.



Main features

▶ A valve with spool detection - the concept

An auto-switch integrated into the valve monitors the spool position and switches on when the spool is in the de-energised position, which is usually the safe state for the application. This indirect monitoring method provides a medium level of diagnostic coverage.

▶ Validated according to ISO 13849-2

This product is capable of meeting the relevant basic and well-tried safety principles.

Please download our reliability data for the details.


▶ SISTEMA library is available

SY safety-related valves data are additionally integrated into the SISTEMA software tool.

Download the library file from our website and be ready to build your safety function.

▶ SY series valves

Benefit from the high versatility this series gives you and create your own configuration, tailored to your needs.



Applications

This valve is ideal for applications using safety architectures that require diagnostics.

How to order

SY5100 - 5 1 - M9 W PC - X30

①
②
③
④
⑤

① Pilot type

—	Internal pilot
R	External pilot

② Light & surge suppressor

—	W/o indicator light & surge suppressor (non-polar)
R	W/surge suppressor (non-polar)
U	W/indicator light & surge suppressor (non-polar)
S	W/surge suppressor (positive common)
Z	W/indicator light & surge suppressor (positive common)
NS	W/surge suppressor (negative common)
NZ	W/indicator light & surge suppressor (negative common)

③ Wiring and output type

N	3-wire, NPN
P	3-wire, PNP
B	2-wire

④ Cable length

S	0.5 m
M	1 m

⑤ Connector specifications

A	M8-3 pins
B	M8-4 pins
D	M12-4 pins

Note) Refer to the reliability data for the latest “How to order”.

Best selling part numbers

Part number	Connector type
SY5100-5U1-M9PWSAPC-X30	M8-3 pins
SY5100R-5U1-M9PWSAPC-X30	M8-3 pins

Valve specifications

Valve type		5 port solenoid valve, spool detection
Valve type		Rubber seal
Type of actuation		2-position single/spring and air return type
Spool detection		Auto switch signal output is on when the spool is in the de-energised position
Fluid		Air
Internal pilot operating pressure range [MPa]		0.15 to 0.7
External pilot operating pressure range [MPa]	Operating pressure range	-100 kPa to 0.7
	Pilot pressure range	0.25 to 0.7
Ambient and fluid temperature [°C]		-10 to 50 (No freezing)
Manual override		Non-locking push type
Max. operating frequency [Hz]		5
Min. operating frequency		1 cycle every 30 days
Lubrication		Not required
Mounting orientation		Unrestricted
Impact/Vibration resistance ¹⁾ [m/s ²]		150/30
Enclosure		IEC60529 standard IP67
Filtration		5 µm filtration or smaller
Coil rated voltage [VDC]		24
Allowable voltage fluctuation [V]		± 10 % of rated voltage (S/Z type -7 % to + 10 %)
Power consumption [W]		0.35 (with indicator light: 0.4)
Surge voltage suppressor		Diode (Varistor for non-polar type)
Indicator light		LED
Pilot exhaust type	Internal pilot	Main/pilot valve common exhaust
	External pilot	Pilot valve individual exhaust

1) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve and armature in both energised and de-energised states every time in each condition. (Values at the initial period)


Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. Test was performed at both energised and de-energised states in the axial direction and at right angles to the main valve and armature. (Values at the initial period)

Auto switch specifications


Auto switch model	D-M9NW	D-M9PW	D-M9BW
Wiring type	3-Wire		2-Wire
Output type	NPN	PNP	—
Applicable load	IC circuit, Relay, PLC		24 VDC relay PLC
Power supply voltage	5, 12, 24 VDC (4.5 to 28 V)		—
Current consumption	10 mA or less		—
Load voltage	28 VDC or less	—	24 VDC (10 to 28 VDC)
Load current	40 mA or less		2.5 to 40 mA
Internal voltage drop	0.8 V or less at 10 mA Load current (2 V or less at 40 mA)		4 V or less
Leakage current	100 µA or less at 24 VDC		0.8 mA or less
Operating time	1 ms or less		—
Indicator light	Green LED when turned on Red LED when within operating range		—
Standard	CE marking, RoHS		—
Electrical entry system	Grommet		—
Lead wire	Oil-proof heavy-duty vinyl cord 2.7 x 3.2 oval, 0.15 mm ² , 2 wire (D-M9BW), 3 wire (D-M9NW/D-M9PW)		—
Withstand voltage	1000 VAC for 1 min (between terminals and housing)		—
Insulation resistance	50 MΩ or more at 500 VDC		—
Ambient temperature	-10 to 60 °C		—
Enclosure	IEC60529 standard IP67, JISC0920 water-proof construction		—

Symbols

SY5100-X30



SY5100R-X30



Manifold flow characteristics ^{1) 2)}

Plug-in metal base

Series	Piping option	Port size		Valve flow-rate characteristics					
		1, 5, 3 (P, EA, EB)	4, 2 (A, B)	1→4/2 (P→A/B)			4/2→5/3 (A/B→E)		
				C [dm ³ /(s·bar)]	b	Q [l/min] (ANR) ³⁾	C [dm ³ /(s·bar)]	b	Q [l/min] (ANR) ³⁾
SY5000	Side ported	1/4	C8	2.6	0.28	653	2.6	0.14	603
	Bottom ported			2.7	0.35	709	2.8	0.20	671

Resin base

Series	Piping option	Port size		Valve flow-rate characteristics					
		1, 5, 3 (P, EA, EB)	4, 2 (A, B)	1→4/2 (P→A/B)			4/2→5/3 (A/B→E)		
				C [dm ³ /(s·bar)]	b	Q [l/min] (ANR) ³⁾	C [dm ³ /(s·bar)]	b	Q [l/min] (ANR) ³⁾
SY5000	Side ported	C10	C8	3.3	0.30	839	3.6	0.17	848
	Bottom ported				0.29	834	4.2	0.26	1042

1) The value is for manifold base with 5 stations and individually operated 2-position type.


2) These values are applicable to rubber seal type valves.

3) These values have been calculated according to ISO 6358 and indicate the flow rate under standard conditions with an inlet pressure of 0.6 MPa (relative pressure) and a pressure drop of 0.1 MPa.


Note

For confirmation of detailed specifications and dimensions, refer to product drawings, instruction manual, reliability data and catalogue at www.smc.eu.


Other related SY products



**5 port solenoid valve with
spring return spool**
SY-X350 Series



**5 port solenoid valve with
detent**
SY-X25 Series



**Pilot air control valve with
spool detection**
SY-X31 Series



**External pilot air control
valve**
SY-X310 Series



Expertise – Passion – Automation

SMC Corporation

Akihabara UDX 15F, 4-14-1
Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN
Phone: 03-5207-8249
Fax: 03-5298-5362

Austria	+43 (0)2262622800	www.smc.at	office@smc.at
Belgium	+32 (0)33551464	www.smc.be	info@smc.be
Bulgaria	+359 (0)2807670	www.smc.bg	office@smc.bg
Croatia	+385 (0)13707288	www.smc.hr	office@smc.hr
Czech Republic	+420 541424611	www.smc.cz	office@smc.cz
Denmark	+45 70252900	www.smc.dk.com	smc@smc.dk.com
Estonia	+372 651 0370	www.smc.ee	info@smc.ee
Finland	+358 207513513	www.smc.fi	smc@smc.fi
France	+33 (0)164761000	www.smc-france.fr	supportclient@smc-france.fr
Germany	+49 (0)61034020	www.smc.de	info@smc.de
Greece	+30 210 2717265	www.smc-hellas.gr	sales@smc-hellas.gr
Hungary	+36 23513000	www.smc.hu	office@smc.hu
Ireland	+353 (0)14039000	www.smc-automation.ie	sales@smc-automation.ie
Italy	+39 03990691	www.smc-italia.it	mailbox@smc-italia.it
Latvia	+371 67817700	www.smc.lv	info@smc.lv

Lithuania	+370 5 2308118	www.smc.lt	info@smc.lt
Netherlands	+31 (0)205318888	www.smc.nl	info@smc.nl
Norway	+47 67129020	www.smc-norge.no	post@smc-norge.no
Poland	+48 222119600	www.smc.pl	office@smc.pl
Portugal	+351 214724500	www.smc.eu	apoiocliente@smc-smc.es
Romania	+40 213205111	www.smcromania.ro	smcromania@smcromania.ro
Russia	+7 (812)3036600	www.smc.eu	sales@smc.ru
Slovakia	+421 (0)413213212	www.smc.sk	office@smc.sk
Slovenia	+386 (0)73885412	www.smc.si	office@smc.si
Spain	+34 945184100	www.smc.eu	post@smc-smc.es
Sweden	+46 (0)86031240	www.smc.nu	smc@smc.nu
Switzerland	+41 (0)523963131	www.smc.ch	info@smc.ch
Turkey	+90 212 489 0 440	www.smc-pnmatik.com.tr	info@smc-pnmatik.com.tr
UK	+44 (0)845 121 5122	www.smc.uk	sales@smc.uk

South Africa	+27 10 900 1233	www.smcza.co.za	zasales@smcza.co.za
---------------------	-----------------	-----------------	---------------------