


1221435
<https://www.phoenixcontact.com/gb/products/1221435>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distribution block, Ex e certified, mounting type: NS 35/7,5, NS 35/15, color: blue

Your advantages

- Ex e certified
- Space savings of up to 50 % on the DIN rail, thanks to transverse mounting
- Flexible use, thanks to DIN rail mounting, direct mounting or adhesive mounting
- Time-saving conductor connection, thanks to tool-free Push-in direct connection technology
- Time savings of up to 80 %, thanks to ready-to-mount blocks without manual bridging
- Clear wiring, thanks to eleven different color variants

Commercial data

Item number	1221435
Packing unit	8 pc
Minimum order quantity	8 pc
Sales key	BEA123
Product key	BEA123
GTIN	4063151309237
Weight per piece (including packing)	33.92 g
Weight per piece (excluding packing)	32.99 g
Country of origin	PL

Technical data

Notes

Notes on operation	the blocks can be bridged with one another via the conductor shaft, for corresponding plug-in bridges, see accessories
--------------------	--

General

Note	The maximum load current of a single clamping unit must not be exceeded.
	For power distribution applications, IEC 60364-4-43:2008; modified + corrigendum Okt. 2008 (DIN VDE 0100-430:2010-10) section 433.2 ff must be observed!

Product properties

Product type	Distributor terminal block
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

Stripping length	8 mm ... 10 mm
------------------	----------------

Ex data

Rated data (ATEX/IECEx)

Identification	Ⓔ II 2 G Ex eb IIC Gb
Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	1204517 SZF 1-0,6X3,5
	3022276 CLIPFIX 35-5
	3022218 CLIPFIX 35
List of bridges	Plug-in bridge / FBS 2-5 / 3030161
Bridge data	23 A (10 mm²)
Ex temperature increase	40 K (40 A / 6 mm²)
Rated insulation voltage	400 V
output	(Permanent)

Ex level General

Rated voltage	440 V
Maximum total current	55 A (10 mm²)
output	(Permanent)

PTFIX 6/12X2,5-NS35A BU-EX - Distribution block



1221435

<https://www.phoenixcontact.com/gb/products/1221435>

Ex level Terminal point

Rated current	22.5 A (2.5 mm ²)
Maximum load current	27 A (4 mm ²)
Contact resistance	0.5 mΩ

Ex connection data Terminal point

Stripping length	8 mm ... 10 mm
Nominal cross section	2.5 mm ²
Rated cross section AWG	14
Connection capacity rigid	0.14 mm ² ... 4 mm ²
Connection capacity AWG	26 ... 12
Connection capacity flexible	0.14 mm ² ... 2.5 mm ²
Connection capacity AWG	26 ... 14
output	(Permanent)

Ex level Feed-in contact

Rated current	40 A (6 mm ²)
Maximum load current	55 A (10 mm ²)
Contact resistance	0.2 mΩ

Ex connection data Feed-in contact

Stripping length	10 mm ... 12 mm
Nominal cross section	6 mm ²
Rated cross section AWG	10
Connection capacity rigid	0.5 mm ² ... 10 mm ²
Connection capacity AWG	20 ... 8
Connection capacity flexible	0.5 mm ² ... 10 mm ²
Connection capacity AWG	20 ... 8

Dimensions

Width	41 mm
Height	45.7 mm
Depth on NS 35/7,5	30.9 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

PTFIX 6/12X2,5-NS35A BU-EX - Distribution block



1221435

<https://www.phoenixcontact.com/gb/products/1221435>

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

Drawings

Circuit diagram



1221435

<https://www.phoenixcontact.com/gb/products/1221435>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1221435>



IECEx

Approval ID: IECExSEV21.0023U



ATEX

Approval ID: SEV21ATEX0557U



CCC

Approval ID: 2022122313115884



UKCA-EX

Approval ID: CML 22UKEX3672U

PTFIX 6/12X2,5-NS35A BU-EX - Distribution block



1221435

<https://www.phoenixcontact.com/gb/products/1221435>

Classifications

ECLASS

ECLASS-13.0	27250118
-------------	----------

ETIM

ETIM 9.0	EC000897
----------	----------

1221435

<https://www.phoenixcontact.com/gb/products/1221435>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk