

Eaton 192318

Catalog Number: 192318

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM3 PXR25, class 1, 630A, 4p, variable, earth-fault protection, ARMS and zone selectivity, withdrawable unit, S, 3

General specifications



Product Name	Catalog Number
Eaton Moeller series NZM molded case circuit breaker electronic	192318
	EAN
	4015081928699
Product Length/Depth	Product Height
346 mm	260 mm
Product Width	Product Weight
230 mm	24.45 kg
Compliances	Certifications
RoHS conform	IEC/EN 60947
	IEC

Product specifications

Type

Circuit breaker

Special features

LSIG overload protection and delayed and non-delayed short-circuit protective device, earth-fault protection
Class 1 energy measurement, r.m.s. value measurement, and "thermal memory"
USB interface for configuration and test function with Power Xpert Protection Manager software
Zone selectivity ZSI
Maintenance Mode ARMS
Interface module in equipment supplied.
Optionally communication-capable with internal Modbus RTU module or CAM
Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn})
Rated current = rated uninterrupted current: 630 A
Terminal capacity hint: Up to 240 mm² can be connected depending on the cable manufacturer.

Application

Use in unearthed supply systems at 690 V

Amperage Rating

630 A

Voltage rating

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Characteristic curve

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-022.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-026.eps](#)

Drawings

[eaton-circuit-breaker-nzm-mccb-dimensions-021.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps](#)

Installation instructions

[eaton-circuit-breaker-basic-unit-bg3-il012100zu.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[DA-CS-nzm3_3p](#)

[DA-CD-nzm3_3p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

690 V - 690 V

Circuit breaker frame type

NZM3

Features

Motor drive optional

Protection unit

Accessories required

NZM3-4-XAVS

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

Withdrawable

Built-in device slide-in technique (withdrawable)

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Equipment heat dissipation, current-dependent

178.61 W

Utilization category

A (IEC/EN 60947-2)

Isolation

500 V AC (between auxiliary contacts and main contacts)

300 V AC (between the auxiliary contacts)

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

40 °C

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part

110

Degree of protection

IP20 (basic degree of protection, in the operating controls area)

IP20

Direction of incoming supply

As required

Electrical connection type of main circuit

Other

Current rating of neutral conductor

0 - 60% - 100% of phase conductor

Lifespan, mechanical

15000 operations

Overvoltage category

III

Degree of protection (IP), front side

IP40 (with insulating surround)

IP66 (with door coupling rotary handle)

Degree of protection (terminations)

IP00 (terminations, phase isolator and strip terminal)

IP10 (tunnel terminal)

Number of poles

Four-pole

Terminal capacity (copper strip)

Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1

mm at rear-side connection (punched)

Min. 6 segments of 16 mm x 0.8 mm at box terminal

Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm

10 segments of 50 mm x 1 mm (2x) at rear-side width extension

Max. 8 segments of 24 mm x 1 mm (2x) at box terminal

Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched)

Lifespan, electrical

5000 operations at 400 V AC-1

3000 operations at 690 V AC-1

5000 operations at 415 V AC-1

Functions

Earth-fault protection

Zone selectivity

Systems, cable, selectivity and generator protection

Integrated earth fault protection

ARMS maintenance mode

Earth-fault current setting (I_g) - max

630 x I_n

Shock resistance

20 g (half-sinusoidal shock 20 ms)

Earth-fault current setting (I_g) - min

126 x I_n

Position of connection for main current circuit

Connection at separate chassis part

Rated operational current for specified heat dissipation (I_n)

630 A

Release system

Electronic release

Short-circuit total breaktime

< 10 ms

Rated short-time withstand current ($t = 0.3$ s)

3.3 kA

Rated short-time withstand current ($t = 1$ s)

3.3 kA

Short-circuit release delayed setting - max

4410 A

Short-circuit release delayed setting - min

378 A

Short-circuit release non-delayed setting - max

5040 A

Short-circuit release non-delayed setting - min

1260 A

Terminal capacity (control cable)

0.75 mm² - 1.5 mm² (2x)

0.75 mm² - 2.5 mm² (1x)

Terminal capacity (copper busbar)

Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection

Max. 10 mm x 50 mm (2x) at rear-side width extension

Min. 20 mm x 5 mm direct at switch rear-side connection

M10 at rear-side screw connection

Terminal capacity (copper solid conductor/cable)

300 mm² (2x) at rear-side width extension

16 mm² (2x) direct at switch rear-side connection

16 mm² (1x) direct at switch rear-side connection

16 mm² (2x) at box terminal

16 mm² (1x) at tunnel terminal

Terminal capacity (aluminum solid conductor/cable)

16 mm² (1x) at tunnel terminal

Terminal capacity (copper stranded conductor/cable)

25 mm² - 120 mm² (2x) at box terminal

25 mm² - 240 mm² (2x) direct at switch rear-side connection

16 mm² - 185 mm² (1x) at 1-hole tunnel terminal

25 mm² - 240 mm² (1x) direct at switch rear-side connection

35 mm² - 240 mm² (1x) at box terminal

Terminal capacity (aluminum stranded conductor/cable)

50 mm² - 240 mm² (2x) at 2-hole tunnel terminal

25 mm² - 185 mm² (1x) at tunnel terminal

50 mm² - 240 mm² (1x) at 2-hole tunnel terminal

Handle type

Rocker lever

Short delay current setting (I_{sd}) - max

7 A

Short delay current setting (I_{sd}) - min

1.5 A

Instantaneous current setting (I_i) - max

10080 A

Instantaneous current setting (I_i) - min

1260 A

Number of operations per hour - max

60

Overload current setting (Ir) - max

630 A

Overload current setting (Ir) - min

252 A

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 230 V, 50/60 Hz

100 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 400/415 V, 50/60 Hz

70 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 440 V, 50/60 Hz

65 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 525 V, 50/60 Hz

18 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 690 V, 50/60 Hz

6 kA

Rated short-circuit making capacity Icm at 400/415 V, 50/60 Hz

154 kA

Rated short-circuit making capacity Icm at 440 V, 50/60 Hz

143 kA

Rated short-circuit making capacity Icm at 525 V, 50/60 Hz

80 kA

Rated short-circuit making capacity Icm at 690 V, 50/60 Hz

50 kA

Standard terminals

Screw terminal

Optional terminals

Box terminal. Connection on rear. Tunnel terminal

Rated short-circuit making capacity Icm at 240 V, 50/60 Hz

220 kA

Rated impulse withstand voltage (Uimp) at auxiliary contacts

6000 V

Rated impulse withstand voltage (Uimp) at main contacts

8000 V

Rated insulation voltage (Ui)
690 V AC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia