

FEATURES

- Good mechanical strength
- Resistant to most chemicals
- Easily fabricated and machined
- Maximum service temperature 60°C

Grey Plastic Sheet, 1000mm x 1000mm x 6mm

RS Stock No.: 704-8204



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO, comes a range of grey PVC sheets. Manufactured to industry standards and being UL DIN 4102 B1 flame resistance, these sheets are of high quality and are great value

General Specifications

Form	Solid
Colour	Grey
Material	PVC
Laminated	Yes
Laminated Material	Acrylic; Epoxy Resin; Fine Weave Cotton; Glass Fibre
Flammability Rating	DIN 4102 B1
Polymer Type	Copolymer, Homopolymer
Finish	Clear
Adhesive Backing	Yes
Applications	These PVC sheet have an array of application use such as; Chemical plant-tanks, Electrical components, Valves and pumps

Electrical Specifications

Specific Surface Resistance	$10^{14} \Omega$
Specific Volume Resistance	$10^{14} \Omega \cdot \text{cm}$
Dielectric Constant	2.9
Dielectric Loss Factor	0.0017tg
Breakdown Voltage	38kV/mm

Mechanical Specifications

Length	1000mm
Width	1000mm
Thickness	6mm
Density	1.47g/cm ³
Tensile Strength	55 MPa
Hardness	Shore D 65 to 80
Water absorption	0.2%
Thermal Conductivity	0.17W/m.K
Elongation	20%
Impact Strength	12kJM ⁻²
Modulus Of Elasticity	3500MPa
Flexural Strength	175MPa
Compression Strength	23MPa
Compression Modulus	3400MPa
Ball Indentation Hardness	253MPa
Thermal Expansion	5x10 ⁻⁵ k ⁻¹
Specific Heat	1.1J/(g.K)
Specific Gravity	1.38
Flexural Modulus	2600MPa
Friction Coefficient	0.54
Poisson Ratio	0.38kJM ⁻²

Operation Environment Specifications

Maximum Operating Temperature	60°C
Melting Point	255°C
Glass Transition Temperature	150°C
Vicat Softening Point	65°C

Approvals

Compliance/Certifications	CE / UR / cUR
Standards Met	UL DIN 4102 B1