


SU9020



Ultrasonic flow meter

SUR54XXBFRKG/US



ACS CE PA cUL US LISTED IO-Link KTW/W270 NSF Reg31

Product characteristics				
Measuring range	1...275 l/min	60...16500 l/h	0.051...13.981 m/s	0.06...16.5 m³/h
Process connection	threaded connection G 1 1/4 external thread DN32			
Application				
Special feature	Gold-plated contacts			
Media	ultra-pure water; water; hydrous media			
Note on media	hydrous media: for media with >10 % additives, the repeatability is the only available value			
Medium temperature	[°C] -20...100			
Min. burst pressure	150 bar		15 MPa	
Pressure rating	100 bar		10 MPa	
Vacuum resistance	[mbar] -1000			
Electrical data				
Operating voltage	[V] 18...32 DC; (to SELV/PELV)			
Current consumption	[mA] < 75			
Protection class	III			
Reverse polarity protection	yes			
Power-on delay time	[s] 5			
Measuring principle	ultrasonic			
Inputs				
Inputs	counter reset			



Ultrasonic flow meter

SUR54XXBFRKG/US

Outputs				
Total number of outputs	2			
Output signal	switching signal; pulse signal; analogue signal; IO-Link; frequency signal; diagnostic signal; totaliser switching signal			
Electrical design	PNP/NPN			
Output function	normally open / normally closed; (parameterisable)			
Max. voltage drop switching output DC [V]	2			
Permanent current rating of switching output DC [mA]	100			
Switching frequency DC [Hz]	0...10000			
Analogue current output [mA]	4...20			
Max. load [Ω]	500			
Pulse output	flow rate meter			
Short-circuit protection	yes			
Type of short-circuit protection	pulsed			
Overload protection	yes			
Measuring/setting range				
Measuring range	1...275 l/min	60...16500 l/h	0.051...13.981 m/s	0.06...16.5 m³/h
Display range	-330...330 l/min	-19800...19800 l/h	-16.777...16.777 m/s	-19.8...19.8 m³/h
Resolution	0.1 l/min	1 l/h	0.001 m/s	0.001 m³/h
Set point SP	2.5...275 l/min	151...16500 l/h	0.128...13.981 m/s	0.151...16.5 m³/h
Reset point rP	1.1...273.6 l/min	65...16414 l/h	0.055...13.908 m/s	0.065...16.414 m³/h
Analogue start point ASP	-275...220 l/min	-16500...13200 l/h	-13.981...11.185 m/s	-16.5...13.2 m³/h
Analogue end point AEP	-220...275 l/min	-13200...16500 l/h	-11.185...13.981 m/s	-13.2...16.5 m³/h
Low flow cut-off LFC	1...13.8 l/min	60...825 l/h	0.051...0.699 m/s	0.06...0.825 m³/h
Frequency end point, FEP	55.2...275 l/min	3310...16500 l/h	2.805...13.981 m/s	3.31...16.5 m³/h
Frequency at the end point FRP [Hz]	1...10000			
Volumetric flow quantity monitoring				
Pulse length [s]	0.002...2			
Pulse value	0.02...99990000 l			
Temperature monitoring				
Measuring range [°C]	-20...100			
Display range [°C]	-44...124			
Resolution [°C]	0.1			
Set point SP [°C]	-19.6...100			
Reset point rP [°C]	-20...99.6			
Analogue start point [°C]	-20...76			
Analogue end point [°C]	4...100			
Frequency start point, FSP [°C]	-20...76			
Frequency end point, FEP [°C]	4...100			
Frequency at the end point FRP [Hz]	1...10000			



Ultrasonic flow meter

SUR54XXBFRKG/US

Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		$\pm (1,0 \% \text{ MW} + 0,5 \% \text{ MEW})$
Repeatability		$\pm 0,2 \% \text{ MEW}$
Temperature monitoring		
Accuracy [K]		$\pm 2,5 (Q > 5 \% \text{ MEW})$
Temperature coefficient [% of the span / 10 K]		0,2
Response times		
Flow monitoring		
Response time [s]		$< 0,25; (dAP = 0, T09)$
Damping process value dAP [s]		0...5
Temperature monitoring		
Dynamic response T05 / T09 [s]		5,7 / 86
Software / programming		
Diagnostic functions		direction of flow detection; signal quality
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1.3
SDCI standard		IEC 61131-9: 2013-07
Profiles	BLOB	Binary Large Object transfer
	Common - I&D	Identification and Diagnosis
Required master port type		A
Process data analogue		3
Process data binary		2
Min. process cycle time [ms]		9.6
IO-Link process data (cyclical)	function	bit length
	totaliser	32
	Flow monitoring	32
	Temperature monitoring	32
	status	4
	Output 1	1
	Output 2	1
Supported DeviceIDs	Type of operation	DeviceID
	default	1637
Operating conditions		
Ambient temperature [°C]		-20...60
Storage temperature [°C]		-25...80
Protection		IP 65; IP 67
Tests / approvals		
EMC	DIN 61326-1:2021	
CPA approval	model number	003US
	accuracy class	1,5



Ultrasonic flow meter

SUR54XXBFRKG/US

Shock resistance	DIN IEC 68-2-27	20 g (11ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000Hz)
MTTF [years]	160	
UL approval	UL approval no.	I034
Pressure Equipment Directive	can be used for group 2 fluids; group 1 fluids on request	

Mechanical data

Weight [g]	639.4
Housing	rectangular
Type of mounting	inlet pipe length 5xDN; outlet pipe length 1xDN
Dimensions [mm]	130 x 48 x 69.5
Materials	housing: stainless steel (316L/1.4404); Display: PFA; Sealing Display: FKM; connector: PBT
Materials (wetted parts)	Pipe section: stainless steel (316L/1.4404); Process connection sealing: NBR reinforced fibre Flat seal
Process connection	threaded connection G 1 1/4 external thread DN32
Surface characteristics Ra/Rz of the wetted parts	Ra < 1.25 µm

Displays / operating elements

Display	colour display 1,44", 128 x 128 pixels
Switching function	2 x LED, yellow
diagnosis	1 x LED, three-colour

Accessories


Items supplied	Flat seal 2, Centellen
	package insert

Remarks

Remarks	MW = measured value
	MEW = Final value of the measuring range
	pulse and totaliser signal are only available for one of the two outputs
	the accuracy indications are adhered to over the entire application area
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated






Ultrasonic flow meter

SUR54XXBFRKG/US

Connection



OUT1/IO-Link:

- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- Pulse output quantity meter
- frequency output volumetric flow quantity monitoring
- frequency output Temperature monitoring
- Diagnostic output direction of flow detection
- Diagnostic output signal quality
- signal output Preset counter

OUT2/InD:

- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- Pulse output quantity meter
- analogue output flow
- analogue output temperature
- Diagnostic output direction of flow detection
- Diagnostic output signal quality
- signal output Preset counter
- input counter reset

colours to DIN EN 60947-5-2


Core colours

- BK= black
- BN= brown
- BU= blue
- WH= white



Diagrams and graphs

derating ambient temperature



- 1 Ambient temperature
- 2 Medium temperature

Pressure loss

