


## LR20AD POWERLINE

IEC DIMENSIONS (MM)







Dimensions	max. (mm)	min. (mm)
A	61.5	
B		59.5
C		18.0
E	1.0	
F	9.5	
G		1.5
Ø	34.2	32.3

## SPECIFICATIONS



Name	LR20 / XL / D / AM1 / MONO / MN1300 / 13A / 13AC
Made in	Belgium
Type	Alkaline foil
Nominal voltage	1.5V
Electrolyte	Potassium Hydroxide
Average weight	142.7g
Storage temperature range	+10°C ~ +25°C
Operating temperature range	-20°C ~ +45°C
Average impedance	approx. 90mΩ @ 1kHz AC
Heavy metals	No added mercury (Hg), Cadmium (Cd) or Lead (Pb)
Compliant with	IEC 60086 non dangerous goods regulation Nordic Ecolabel (White Swan) version 3.7 EC directive 91/157EC, 98/101EC, 2006/66/EC
Recommended cut-off voltage	0.8V per cell

## LR20AD POWERLINE

### TYPICAL DISCHARGE VALUES



### DISCHARGE TEMPERATURE CHARACTERISTICS



\*1 High intention flashlight    \*2 Light intention flashlight

## LR20AD POWERLINE

## DISCHARGE TEMPERATURE CHARACTERISTICS

