

25.4mm (1.0 INCH) SINGLE DIGIT NUMERIC DISPLAY

Part Number: SC10-21EWA

High Efficiency Red


Features

- 1.0 inch digit height.
- Low current operation.
- Excellent character appearance.
- High light output.
- Easy mounting on P.C. boards or sockets.
- Mechanically rugged.
- Standard : gray face, white segment.
- RoHS compliant.


Description

The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

Package Dimensions& Internal Circuit Diagram











Notes

1. All dimensions are in millimeters (inches), Tolerance is ±0.25(0.01")unless otherwise noted.

2. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

SPEC NO: DSAM9670 REV NO: V.1A
APPROVED: WYNEC CHECKED: Joe Lee

DATE: APR/20/2013 DRAWN: Q.M.Chen PAGE: 1 OF 7 ERP: 1301000787

Selection Guide

Part No.	Dice	Lens Type	Iv (ucd) [1] @ 10mA		Description
			Min.	Тур.	
SC10-21EWA	High Efficiency Red (GaAsP/GaP)	White Diffused	14000	23000	Common Cathode, Rt. Hand Decimal.
			*3600	*6500	

Note:

- 1. Luminous intensity/ luminous Flux: +/-15%.

 * Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red	627		nm	I==20mA
λD [1]	Dominant Wavelength	High Efficiency Red	617		nm	I=20mA
Δλ1/2	Spectral Line Half-width	High Efficiency Red	45		nm	IF=20mA
С	Capacitance	High Efficiency Red	15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage (DP)	High Efficiency Red	4.0 (2.0)	5.0 (2.5)	V	I=20mA
lR	Reverse Current (Per chip)	High Efficiency Red		10 (10)	uA	V _R =5V (V _R =5V)

Notes:

- 1.Wavelength: +/-1nm.
- Forward Voltage: +/-0.1V.
 Wavelength value is traceable to the CIE127-2007 compliant national standards.


Absolute Maximum Ratings at TA=25°C

Parameter	High Efficiency Red		
Power dissipation (DP)	150 (75)	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	160	mA	
Reverse Voltage (Per chip)	5 (5)	V	
Operating / Storage Temperature	-40°C To +85°C		
Lead Solder Temperature[2]	260°C For 3-5 Seconds		


Notes:


- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.


SPEC NO: DSAM9670 **REV NO: V.1A** DATE: APR/20/2013 PAGE: 2 OF 7 APPROVED: WYNEC **CHECKED:** Joe Lee DRAWN: Q.M.Chen ERP: 1301000787




High Efficiency Red SC10-21EWA













 SPEC NO: DSAM9670
 REV NO: V.1A
 DATE: APR/20/2013
 PAGE: 3 OF 7

 APPROVED: WYNEC
 CHECKED: Joe Lee
 DRAWN: Q.M.Chen
 ERP: 1301000787










 SPEC NO: DSAM9670
 REV NO: V.1A
 DATE: APR/20/2013
 PAGE: 4 OF 7

 APPROVED: WYNEC
 CHECKED: Joe Lee
 DRAWN: Q.M.Chen
 ERP: 1301000787




SPEC NO: DSAM9670 APPROVED: WYNEC REV NO: V.1A CHECKED: Joe Lee DATE: APR/20/2013 DRAWN: Q.M.Chen PAGE: 5 OF 7 ERP: 1301000787

THROUGH HOLE DISPLAY MOUNTING METHOD

Lead Forming

Do not bend the component leads by hand without proper tools. The leads should be bent by clinching the upper part of the lead firmly such that the bending force is not exerted on the plastic body.




Installation

- 1. The installation process should not apply stress to the lead terminals.
- 2. When inserting for assembly, ensure the terminal pitch matches the substrate board's hole pitch to prevent spreading or pinching the lead terminals.




3. The component shall be placed at least 5mm from edge of PCB to avoid damage caused excessive heat during wave soldering.



SPEC NO: DSAM9670 APPROVED: WYNEC REV NO: V.1A CHECKED: Joe Lee DATE: APR/20/2013 DRAWN: Q.M.Chen PAGE: 6 OF 7 ERP: 1301000787

DISPLAY SOLDERING CONDITIONS

Wave Soldering Profile For Lead-free Through-hole LED.



NOTES:

- 1.Recommend the wave temperature 245°C~260°C.The maximum soldering temperature should be less than 260°C.
- 2.Do not apply stress on epoxy resins when temperature is over 85°C.
- 3. The soldering profile apply to the lead free soldering (Sn/Cu/Ag alloy).
- 4.During wave soldering , the PCB top-surface temperature should be kept below 105°C
- 5.No more than once.

Soldering General Notes:


- 1. Through—hole displays are incompatible with reflow soldering.
- 2. If components will undergo multiple soldering processes, or other processes where the components may be subjected to intense heat, please check with Kingbright for compatibility.

CLEANING

- 1.Mild "no-clean" fluxes are recommended for use in soldering.
- 2. If cleaning is required, Kingbright recommends to wash components with water only. Do not use harsh organic solvents for cleaning, because they may damage the plastic parts .And the devices should not be washed for more than one minute.

CIRCUIT DESIGN NOTES

- 1.Protective current-limiting resistors may be necessary to operate the Displays.
- 2.LEDs mounted in parallel should each be placed in series with its own current—limiting resistor.



All design applications should refer to Kingbright application notes available at http://www.KingbrightUSA.com/ApplicationNotes

 SPEC NO: DSAM9670
 REV NO: V.1A
 DATE: APR/20/2013
 PAGE: 7 OF 7

 APPROVED: WYNEC
 CHECKED: Joe Lee
 DRAWN: Q.M.Chen
 ERP: 1301000787