

Features

- The lockout device rotates freely around the valve hand wheel when locked, effectively preventing the valve from being turned.
- Made from strong Polyurethane plastic, providing resistance to cracking, abrasion, extreme weather, and temperature conditions.
- Gate valve lockout device has three padlock holes, allowing for secure locking with padlock.
- Accommodates rising stem valves, adding versatility for different types of valve systems.
- Compatible with hasps and padlocks, allowing multiple layers of security.
- Suitable for use in various industrial and maintenance settings where valve isolation is required.

RS PRO Gate Valve Lockout - For Handle Wheel Dia 254 To 355 mm

RS Stock No.: 0750829



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Durable Polyurethane Construction* – Built from tough polyurethane plastic that is resistant to cracking and abrasion, ensuring long-term, rugged performance in industrial environments.
- *Rotating Locking Mechanism* – Once applied and locked, the cover rotates freely around the valve handwheel, preventing unauthorised operation and keeping the valve securely locked.
- *Padlock-Ready Design* – Equipped with padlock holes, compatible with standard lockout hasps and padlocks, supporting single or multiple user lockouts.
- *Versatile Application* – The knockout centre design allows accommodation of OS & Y (rising stem) valves, increasing compatibility with different valve types and installations.
- *Secures Valve in Closed Position* – Designed specifically to lock gate valves in the closed position, preventing accidental reactivation during maintenance or service.
- *Enhanced Safety & Compliance* – Provides an effective way to comply with LOTO (Lockout Tagout) protocols, enhancing workplace safety during mechanical isolation procedures.

General Specifications

Type	Gate Valve Lockout
Material	Polyurethane Plastic
Colour	Red
Padlock holes	3
Package	LD

Mechanical Specifications

Outside Dia (A)	368mm
Neck Dia (B)	103mm
Inside Dia (C)	355mm
Inside Depth (D)	64mm
Outside Depth (E)	74mm
Weight	950 Grams

Operation Environment Specifications

Withstand temperature	-20°C to 90°C.
-----------------------	----------------

