

F100 METALS

Cutting or Grinding Disc - Expert +++

Composition Characteristics

- Grain: A (aluminum oxide)
- Grain size: 46 (medium)
- Hardness: S (hard)
- Bond: BF (reinforced resin)

Dimensions / Thicknesses / Bore

Ø76: 1 - 1.6 - 1.8 - 3 - 5 - 6.4 mm / 10 mm bore
Ø115: 1.6 - 3 - 6.4 mm / 22.23 mm bore
Ø125: 1.6 - 2.5 - 3 - 6.4 mm / 22.23 mm bore
Ø230: 2 - 2.5 - 3 - 6.4 mm / 22.23 mm bore
Ø250: 3 mm / 25.40 mm bore
Ø300: 2.8 - 3.5 mm / 20 - 25.40 mm bore
Ø350: 2.8 - 4 mm / 20 - 25.40 mm bore
Ø400: 4 mm / 25.40 mm bore

Number of fiberglass reinforcements: 2 for cutting and 3 for grinding.

Application: For cutting metals and stainless steel.

Benefits

- Intensive cutting performance.
- Fast and clean cut.

Standards and Safety

Working speed: 80 m/s
EN 12413
Types 41, 27 and 42.

SEA Abrasifs - 113 rue Combe de Veyle, 01750 Replonges, France - +33 (0)3 85 31 18 40 - commercial@sea-abrasifs.com - sea-abrasifs.com