

# Impact Driver XGT®, 40Vmax

## TD003G

1/4", 210 Nm, 0 – 3 700 min<sup>-1</sup>

**Model TD003G is a cordless impact driver powered by 40Vmax XGT® Li-Ion battery**

It features a combination of sufficient fastening performance and high cost-competitiveness achieved by carefully selecting the functions. The main features and benefits are: Aluminum hammer case + Black bumper, Impact power selection: 4 modes (Max/ Hard/ Med./ Soft for bolt), 1 T-mode (for thin metal only)



### Technical specifications

|                                         |                                                    |
|-----------------------------------------|----------------------------------------------------|
| Nominal Battery Voltage                 | 40 V                                               |
| Voltage XGT                             | ✓                                                  |
| Brushless Motor                         | ✓                                                  |
| No load speed                           | 0 - 1100 / 2100 /<br>3200 / 3700 min <sup>-1</sup> |
| Max Fastening Torque Impact Drill       | 20 / 50 / 170 / 210<br>Nm                          |
| Tightening Capacity Standard Bolt       | M5 - M16                                           |
| Impacts per Minute (IPM)                | 0 - 1400 / 2600 /<br>3600 / 4100 min <sup>-1</sup> |
| Sound Power Level (L <sub>WA</sub> )    | 106 dB(A)                                          |
| Sound Pressure Level (L <sub>pA</sub> ) | 98 dB(A)                                           |
| Noise Uncertainty (K Factor)            | 3 dB(A)                                            |
| Tool weight with battery                | 1,7 - 2,9 kg                                       |
| Product Dimensions (L x W x H):         | 121 x 86 x 252 mm                                  |
| Battery Chemistry (Ni-Cd / Ni-MH / Li-  | Li-ion                                             |

### User benefits

- LED light illuminates the work site
- Low power consumption thanks to brushless motor
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- The rubber coating on the handle ensures a firm working grip
- Battery protection system automatically shuts off power when the battery level is low
- Anti wobbling bit structure

Link to product - [www.makitauk.com](http://www.makitauk.com)



# Related products

## Other

User manual

Parts drawing