

## FEATURES

- Reinforced doors that prevent distortion
- They also feature lockable chrome 'L' plated handle with 2 keys
- The integral non-removeable spillage
- They have been designed with a fully welded construction

## RS PRO Grey Steel Lockable 2 Doors COSHH Cabinets, 915mm x 915mm x 457mm

RS Stock No.: 424-5516



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Introducing the RS PRO range of COSHH Hazardous Substance Storage Cabinets. These high-quality, leakproof cabinets are ideal for the safe storage of flammable liquids, paints, pesticides and many other hazardous substances. The cabinet features a welded body which stops any leakage from the substances stored within the cabinet, ensuring that any hazardous substances are not exposed to the area they are kept in. These cabinets are essential to ensure COSHH regulations, as well as various other regulations to do with storing hazardous and flammable substances, are met.

What other cabinets are in this RS PRO range?

[424-5500](#) 457 x 457 x 305 mm 1 Shelf  
[424-5493](#) 915 x 457 x 457 mm 1 Shelf  
[424-5516](#) 915 x 915 x 457 mm 1 Shelf  
[424-5522](#) 1219 x 915 x 457 mm 2 Shelves  
[424-5538](#) 1829 x 915 x 457 mm 3 Shelves

## General Specifications

<b>Number of Doors</b>	2
<b>Number of Shelves</b>	1
<b>Lockable</b>	Yes
<b>Material</b>	Steel
<b>Colour</b>	Grey
<b>Finish</b>	Epoxy polyester powder coat
<b>Applications</b>	Schools, Hospitals, Science laboratories, Factories and Offices, Cleaning cupboards

## Mechanical Specifications

<b>External Size</b>	915mm x 915mm x 457mm
<b>Height</b>	915mm
<b>Width</b>	915mm
<b>Depth</b>	457mm
<b>Locking Mechanism</b>	Two steel locking rods top and bottom, supplied with two keys

## Approvals

### Compliance/Certifications

HSG51 – Storage of Flammable Liquids in Containers, DSEAR Approved Code of Practice L136 paragraphs 94-96 along with Appendices A and B and paragraph 104

