



3199 - MALE STUD ELBOW BSPP METRIC AND UNF THREAD



maximum working pressure	20 bar 2 MPa 290 psi
working temperature	-20 to 80 °C -4 to 176 °F 253 to 353 °K
vacuum capability	755 mm Hg
body	TECHNICAL POLYMER
sub-base	NICKEL PLATED BRASS
'O'-rings	NBR
gripping ring	STAINLESS STEEL

Part Nb	ØD (MM)	C	E (mm)	F (mm)	ØG (mm)	H (mm)	L (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
3199 03 09	3	M3x0,5	2.5	8	8.5	15	14.5	.003
3199 03 19	3	M5x0,8	3.5	8	8.5	13.5	14.5	.003
3199 04 09	4	M3x0,5	2.5	8	8.5	15	14.5	.003
3199 04 10	4	G1/8	5	13	8.5	13	14	.006
3199 04 13	4	G1/4	5.5	16	8.5	13	14	.01
3199 04 19	4	M5x0,8	3.5	8	8.5	13.5	14	.002
3199 04 55	4	M7x1	4.5	10	8.5	15	14	.005
3199 06 10	6	G1/8	5	13	10.5	15	16	.006
3199 06 13	6	G1/4	5.5	16	10.5	15	16	.011
3199 06 17	6	G3/8	5.5	20	10.5	15.5	16	.022
3199 06 19	6	M5x0,8	3.5	8	10.5	15.5	16	.003
3199 06 21	6	G1/2	7	24	10.5	16	16	.027
3199 06 55	6	M7x1	4.5	10	10.5	17.5	16	.005
3199 06 60	6	M10x1	5	13	10.5	15	14	.006
3199 06 67	6	M12x1,5	5.5	15	10.5	15	16	.009
3199 08 10	8	G1/8	4.5	13	13.5	20.5	23	.009
3199 08 13	8	G1/4	5.5	16	13.5	18.5	23	.012
3199 08 17	8	G3/8	5.5	20	13.5	18.5	23	.017
3199 08 21	8	G1/2	7	24	13.5	19	23	.027
3199 08 60	8	M10x1	5	13	13.5	20.5	23	.009
3199 08 67	8	M12x1,5	5.5	15	13.5	18	23	.009
3199 10 13	10	G1/4	5.5	16	16	23.5	26.5	.014
3199 10 17	10	G3/8	5.5	20	16	22	26.5	.017
3199 10 21	10	G1/2	7	24	16	22	26.5	.027
3199 12 13	12	G1/4	5.5	16	19	26.5	31	.016
3199 12 17	12	G3/8	5.5	20	19	25	31	.019
3199 12 21	12	G1/2	7	24	19	25	31	.029
3199 14 17	14	G3/8	5.5	20	22	32.5	35.5	.029
3199 14 21	14	G1/2	7	24	22	27	35.5	.028
3199 16 17	16	G3/8	7.5	27	27	54.5	39	.101
3199 16 21	16	G1/2	9	27	27	54.5	39	.097