




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Primary Product Color: **Black**

Protection & Strain Relief Accessory Type: **Cover Assembly**

Primary Product Material: **PBT GF20**

Strain Relief: **Without**

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Cover Assembly

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF20

Mechanical Attachment

Strain Relief	Without
---------------	---------

Packaging Features

Packaging Method	Box
Packaging Quantity	300

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1534181-1
MCP1,5 REC HSG10P



TE Part # 1534180-1
MCP REC HSG ASSY32P

Customers Also Bought



TE Part #1534841-1
COVER FOR 12POS,MQS



TE Part #2208716-1
PLATE,FAMILY SEAL COVER,91POS



TE Part #2-1241418-3
AMP MCP 6.3/4.8K, CONTACT, SWS



TE Part #CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part #968182-1
JPT/MT3 BU-GEH 4P

TE Part #2112674-4
37POS MIXED MQS REC COD D

TE Part #2112675-3
36POS MIXED MQS REC COD C

TE Part #2112675-1
36POS MIXED MQS REC COD A

TE Part #2208436-1
17POS, MIXED, REC HSG, WITH HSD

Documents

Product Drawings
COVER,32POSN., REC HSG,ASSY
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2141411-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2141411-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2141411-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification
English